## 1500 g x 0.05 g DIGITAL BALANCE

Model: GM-1500P *ISO-9001, CE, IEC1010* 







The Art of Measurement

## DIGITAL BALANCE, 1500 g x 0.05 g

Model: GM-1500P

\* Heavy duty ABS housing plastic case.

FFATURE				
FEATURES				
Microprocessor circuit with high accuracy & better performance.				
* High resolution & wide measuring capacity, 1500 g x 0.05 g, 50 oz x 0.002 oz.				
* Large LCD display, 20.9 mm (0.8") digit size, easy read out.				
Built-in gram & oz display unit, select by the internal slide switch.				
* Built-in self calibration system, the calibration value can memorize into EEPROM				
circuit permanently even power off.				
Counting scale function.				
RS232/USB computer interface.				
Accept battery or AC/DC adapter power source, two way power supply.				

SPECIFICATIONS				
Display	LCD, 20.9 mm (0.8") digit size, 5 digits with annunciator.			
Function	Weighting & counting.			
Weighting range &	Unit	Range	Resolution	
resolution	g	0.50 g to 1500 g	0.05 g	
	OZ	0.02 oz to 49.998 oz	0.002 oz	
		50 oz to 52.8 oz	0.005 oz	
Min. display weight	g	0.50 g		
	OZ			
Unit select	g or oz, select by internal slide switch.			
Accuracy	± (0.05 % + 0.2g)			
	* Within two hours after self calibration be executed at 23 $\pm$ 5 $^{\circ}$ C			
	* Spec. tested under the environment RF Field Strength less than 3 V/M and			
	frequency less than the 30 MHz only.			
Sampling time	Approx. 1 second.			
Tare control	Approx. 1500 g max.			
Transducer	Load cell.			
Circuit	Microprocessor circuit.			
Auto self calibration	Use 500 g or 1000 g standard weight to execute self-calibration			
	automatically.			
Data Output	RS 232/USB PC computer interface.  * Connect the optional RS232 cable UPCB-02 will get the RS232 plug.			
	* Connect the optional USB cable USB-01 will get the USB plug.			
Counting sample no.	10 PCs, 20 PCs, 50 PCs or 100 PCs.			
Operating temperature	0 to 50 $^{\circ}\mathrm{C}$ ( 32 to 122 $^{\circ}\mathrm{F}$ ).			
Operating humidity	Less than 80% RH.			
Size	Cabinet 250 x 190 x 70 mm.			
	Platform 185 x 185 mm.			
Power Supply	6 x 1.5V A	A (UM-3) battery x 6 PCs,		
	or DC 9V adapter ( optional ).			
Power Consumption	Approx. DC 17 mA.			
Accessory Included	Operation Manual1 PC.			
Optional Accessories				
	* RS232 cable, UPCB-02.			
	* USB cable, USB-01.			
	* AC/DC 9V power adapter, AP-9VA.			

<sup>\*</sup> Appearance and specifications listed in this brochure are subject to change without notice.