

## Product information

# 02 06 225

## High Leverage Combination Pliers

DIN ISO 5746 IEC 60900 DIN EN 60900



- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- Precise, minimal light gap between the gripping jaws to ensure optimal function of the cutting edges
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

### General

|                 |  |
|-----------------|--|
| Article No.     | 02 06 225  |
| EAN             | 4003773010036                                    |
| Pliers          | chrome-plated                                    |
| Head            | chrome-plated                                    |
| Handles         | insulated with multi-component grips, VDE-tested |
| Weight          | 425 g  |
| Dimensions      | 225 x 58 x 29 mm                                 |
| Standard        | DIN ISO 5746 DIN EN 60900 IEC 60900              |
| REACH compliant | does not contain SVHC                            |
| RoHS compliant  | not applicable                                   |

### Technical details

|  |                      |
|--|----------------------|
| Cutting capacities hard wire (diameter)          | Ø 3.0 mm             |
| Cutting capacities piano wire (diameter)         | Ø 2.5 mm             |
| Cutting capacity copper cable, multiple-stranded | Ø 14.0 mm            |
| Cutting capacity copper cable, multiple-stranded | 25.0 mm <sup>2</sup> |
| VDE tested                                       | yes                  |

*technical change and errors excepted*



