

Start Surface IP66 Ø300mm New

START SURFACE IP66 1250LM 840 IK10 BLK
0049927



Product features

- LED exterior surface mounted luminaire, 1250lm, 12W power consumption, 104lm/W efficacy, 4000K color temperature, CRI80, non-dimmable, IP66, IK10, 90,000 hours (L70B50) Lifespan, black housing, vandal resistant, supplied with anti-theft screws



PRODUCT OVERVIEW

Product name	START SURFACE IP66 1250LM 840 IK10 BLK
Technology	LED
Cap/Base	N/A
Housing	PC Polycarbonate
Mount	Ceiling surface mounting, Wall surface mounted
Environment	Indoor, Outdoor
General application	Hospitality
ETIM Class	EC002892
E-number FI	4579598
Warranty	5 years
Fixture luminous flux (lm)	1250
Luminaire efficacy (lm/W)	105
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Photobiological Risk Group	RG0
Total power consumption (W)	12
Electrical protection	Class II
Control gear type	LED driver constant current
Dimmable	No
Dimming method	N/A
Housing colour	RAL 9011 - Graphite black
IP rating	IP66
IK rating	IK10
Product EAN number	5410288499277

DATA TABLE

General data

Product name	START SURFACE IP66 1250LM 840 IK10 BLK
Technology	LED
Cap/Base	N/A

Start Surface IP66 Ø300mm New *START SURFACE IP66 1250LM 840 IK10 BLK* 0049927

Housing	PC Polycarbonate
Mount	Ceiling surface mounting, Wall surface mounted
Environment	Indoor, Outdoor
General application	Hospitality
Operating temperature range (°C)	-20°C...+40°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
E-number FI	4579598
Warranty	5 years

Optical data

Fixture luminous flux (lm)	1250
Luminaire efficacy (lm/W)	105
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Distribution type	Diffuse, Symmetric
Photobiological Risk Group	RG0

Electrical data

Total power consumption (W)	12
Mains voltage (V)	220-240V
Lamp power factor	0.83
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	15
Electrical protection	Class II
Control gear type	LED driver constant current
No. Of switching cycles before premature failures	>50000
Dimmable	No
Dimming method	N/A
Inrush Current (A)	20
Glow Wire Test (°C)	650
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz
Max. Luminaires per 10A C Breaker	38
Max. Luminaires per 13A C Breaker	47
Max. Luminaires per 16A C Breaker	57
Max. Luminaires per 20A C Breaker	66
Max. Luminaires per 10A B Breaker	30
Max. Luminaires per 13A B Breaker	38
Max. Luminaires per 16A B Breaker	45

Lifetime data

Lifespan L70 B50	90000
Lifespan L80 B50	78000

Start Surface IP66 Ø300mm New START SURFACE IP66 1250LM 840 IK10 BLK 0049927

Physical data

Housing colour	RAL 9011 - Graphite black
IP rating	IP66
IK rating	IK10
Diffuser finish	Diffuse
Diffuser material	PC Polycarbonate
Nominal Product Height (mm)	90
Nominal Product Diameter (mm)	300
Weight (kg)	0.78


Packaging

Single packaging type	Carton
Product EAN number	5410288499277
Packaging single length / height (cm)	30.2
Packaging single width (cm)	9.9
Packaging single depth (cm)	30.5
DUN14 (outer)	15410288499274
Units per outer package	6
Packaging outer length / height (cm)	61.5
Packaging outer width (cm)	31.0
Packaging outer depth (cm)	32.0

Safety data

Optimal operating condition (°C)	-20-40
----------------------------------	--------

PHOTOMETRY



TECHNICAL DRAWINGS

Start Surface IP66 Ø300mm New
START SURFACE IP66 1250LM 840 IK10 BLK
0049927

