

High-performance drill SC TiAlNplus HPC 8xD with internal cooling HA

for universal use up to 1300 N/mm²



Application

for HPC boring up to a strength of 1300 N/mm²

Version

- solid carbide TiAlNplus high-performance drill
- 4 drill heels
- Four grinding faces
- 30° spiral angle
- Straight main cutting edge

Advantage

- economic drilling in a wide variety of materials with high cutting values
- newly developed geometry in conjunction with a multi-layer coating individually tailored to drilling ensures significantly longer service lives
- Cutting edge finishing reduces micro-fractures and increases the service life
- very high alignment accuracy thanks to 4 drill heels
- high process reliability even at extreme depths

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas-tics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
	135	110	90	35	30	210	260	230	180	160	130	60		110	40	35	30		

Art. No.	11108 054
Cutting edge diameter	5.4 mm
Tolerance of cutting edge diameter	h7
Cutting material	VHM
Surface	TiAlN plus
Max. drilling depth (D)	8xD
Type	HPC UNI
Coolant supply	Internal
Tool holding device	HA parallel shank
Angle of the tip	135 Degree
Shaft diameter	6 mm
Chip flute length	57 mm
Length	95 mm
f steel 1000	0.11 mm/r

EAN-Code

4050293530636