

## DVUN steel boring bar, negative right

For copy and longitudinal turning with VN indexable insert

**WIDIA** 

### Application:

For copy and longitudinal turning with VN indexable insert, 35°

### Execution:

- Precision-manufactured steel boring bar, internal cooling, type V, pitch angle 93°, tip angle 35°, clearance angle 0°

### Advantage:

- Very slim geometry, optimised for contouring
- Negative body geometry ensures good stability and absorption of force for large cutting depths
- Wide adjustment range: Suitable for both finishing and rough machining



<b>Art. no.</b>	<b>17684 013</b>
<b>Brand</b>	WIDIA
<b>Manufacturer Part Number</b>	5696263
<b>ISO name</b>	A 32 S DVUN R/L 16
<b>Min. bore diameter</b>	40 mm
<b>Shank diameter</b>	32 mm
<b>Length</b>	250 mm
<b>Programming size</b>	22 mm
<b>Suitable for indexable inserts</b>	VN.. 1604..
<b>Tool design</b>	Right
<b>Gross Weight</b>	1.373 kg
<b>Product Group</b>	1XG

### EAN

4050841470643