

## Drilling machine vices BOF

Mechanical clamping system, manually operated



### Application:

Secure clamping and fixing of workpieces on drills and measuring machines

### Execution:

- Made from grey cast iron
- Means of attachment on side and front face
- Long guide for the moving jaws also in outer clamping range
- Both jaws have a support surface for clamping flat workpieces
- Clamping jaws are reversible, one side is smooth or has longitudinal and lateral vee blocks, and the other side is knurled and polished on both sides



### Delivery:

1 pc. Drill vice BOF

<b>Art. no.</b>	<b>28681 160</b>
<b>Brand</b>	RÖHM
<b>Manufacturer Part Number</b>	111597
<b>Jaws width</b>	160 mm
<b>Clamping width</b>	220 mm
<b>Jaws height</b>	50 mm
<b>Body length</b>	445 mm
<b>Height</b>	95.5 mm
<b>Chip flute width</b>	17 mm
<b>Weight</b>	25 kg
<b>Gross Weight</b>	24.600 kg
<b>Product Group</b>	203

### EAN

4019208039442