

## Roller container with vice holder plate

With 4 fully extending drawers

### Execution:

- Welded sheet steel structure with 4 rubber-tyred wheels, 2 of which are fixed wheels (diameter 300 mm) and 2 of which are steering rollers (diameter 200 mm), lockable
- With large folding steel tube push handle
- Top of deposit tray fitted with a ribbed rubber mat
- Tilt-proof due to built-in individual drawer pull-out lock
- Delivered without vice, please order separately (see no. 51028001 ATORN parallel vice, jaw width 100 mm)
- Vice can be attached to the upper frame of the trolley (carrier plate provided on frame)
- For suitable insert materials for drawers, see from no. 50485 060-265 and no. 50537 610-695
- Other equipment options available at extra cost: SOFT-CLOSE for drawers, see no. 50392 005, ELECTRONIC CODE combination lock, see no. 50392 010



<b>Art. no.</b>	<b>50282 182</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	50282182
<b>Number of drawers</b>	4 PCS
<b>Pullout type</b>	Full extension
<b>Number of loading surfaces</b>	1 PCS
<b>Drawer front height</b>	2 x 60 mm, 1 x 90 mm, 1 x 120 mm
<b>Height</b>	930/800 mm
<b>Width</b>	570 mm
<b>Depth</b>	680 mm
<b>Drawer width (inner dimension)</b>	450 mm
<b>Drawer depth (inner dimension)</b>	600 mm
<b>Load-carrying capacity per drawer</b>	70 kg
<b>With single pull-out safety brake</b>	Yes
<b>Central locking</b>	Yes
<b>Lock type</b>	DOM® locking system
<b>With sliding handle</b>	Yes
<b>Load-carrying capacity</b>	910 kg
<b>Number of fixed rollers</b>	2 PCS
<b>Number of steering rollers</b>	2 PCS
<b>Number of wheel adjusters</b>	2 PCS
<b>Material of wheel</b>	Solid rubber
<b>Wheel diameter</b>	300/200 mm
<b>Material</b>	Sheet steel
<b>Cabinet colour</b>	Light grey RAL 7035
<b>Colour of front</b>	Gentian blue RAL 5010
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	72.000 kg
<b>Product Group</b>	501

### EAN

4039247969586