

50830  ACTIVE

STRATO-THERM | STRATO-THERM

TE Internal #: 50830

STRATO-THERM, Ring Terminals & Spade Terminals, Ring Tongue,  
26 – 24AWG Wire Size, .12 – .24mm<sup>2</sup> Wire Size, #6 / M3.5, Stud

Diameter 3.68 mm [.145 in]

[View on TE.com >](#)



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: .12 – .24 mm<sup>2</sup>

Ring & Spade Stud Size: #6, M3.5

Stud Diameter: 3.68 mm [.145 in]

## Features

### Product Type Features

Shape Description	RING-052
Ring & Spade Stud Size	#6, M3.5
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

### Configuration Features

Number of Holes	1
Terminal Angle	Straight

### Electrical Characteristics

Voltage (Max)	300 V
---------------	-------

### Body Features

Weight per Piece	4.536 g
Ring & Spade Plating Material	Copper, Nickel

### Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Offset



### Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

### Dimensions

Wire Size	.12 – .24 mm <sup>2</sup>
Stud Diameter	3.68 mm [.145 in]
Tongue Thickness	.5 mm [.02 in]
Ring & Spade Overall Length	18.8 mm [.74 in]
Ring & Spade Wire Insulation Diameter (Max)	2.08 mm [.082 in]
Ring & Spade Wire Insulation Diameter	.81 – 2.08 mm [.032 – .082 in]

### Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	288 °C [550 °F]

### Operation/Application

Heavy Duty	No
------------	----

### Industry Standards

Government Qualified	No
----------------------	----

### Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


## Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Compatible Parts



## Also in the Series | STRATO-THERM



## Customers Also Bought





TE Part #1-6450869-4  
V/R 2ACP+1LP+32S+3HDP+1LP+1P



TE Part #103639-4  
05 MTE HDR SRST LATCH .100CL



TE Part #1410972-3  
MULTIGIG RT2 7RW H-LFT, SE



TE Part #1648156-1  
242-27-01100



TE Part #1-51864-0  
PIDG RING TONGUE TERMINALS



TE Part #YDTS26F25-29PA0000  
D38999: Straight Plug, 25-29 Insert

## Documents

### Product Drawings

[TERMINAL,PIDG PTFE R 26-24 6](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_50830\\_N.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_50830\\_N.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_50830\\_N.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Datasheets & Catalog Pages

[STRATO-THERM Terminals & Splices for High Temperature Applications](#)

English

### Product Specifications

[Application Specification](#)

English