

ERSADUR long-life soldering tip series 832 and 842



- ANALOG 60/60 A
- ANALOG 80/80 A
- DIGITAL 80 A
- DIGITAL 2000 A with POWER TOOL soldering iron
- ELS 8000/M/D

- Ersä 15+ / 25+ / 35+
- MICRO-CON 60 iA with POWER TOOL soldering iron
- MS 6000 / MS 8000/D
- Multi-Pro
- Multi-Sprint

- Multi-TC
 - RDS 80
 - TWIN 80 A
- with Ergo Tool soldering iron

<p>0832UD/UDLF</p> <p>pencil point, 0.4 mm ϕ, extended</p>	<p>0832SD/SDLF</p> <p>pencil point, 0.8 mm ϕ, extended</p>	<p>0832BD/BDLF</p> <p>pencil point, 1.0 mm ϕ</p>	<p>0832YD/YDLF</p> <p>chisel-shaped, 1.6 mm</p>
<p>0832CD/CDLF</p> <p>chisel-shaped, 2.2 mm</p>	<p>0832KD/KDLF</p> <p>chisel-shaped, 2.2 mm, extended</p>	<p>0832ED/EDLF</p> <p>chisel-shaped, 3.2 mm</p>	<p>0832VD/VDLF</p> <p>chisel-shaped, 5.0 mm</p>
<p>0832FDLF</p> <p>angled face, 2.0 mm</p>	<p>0832TDLF</p> <p>angled face, 3.0 mm ϕ</p>	<p>0832NDLF</p> <p>angled face, 4.0 mm ϕ</p>	<p>0832PW</p> <p>PowerWell with concave portion</p>
<p>0832HD</p> <p>SolderWell with concave portion, bent</p>	<p>0832AD</p> <p>PLCC blade, 1.5 mm</p>	<p>0852OD</p> <p>PLCC blade, 2.0 mm</p>	<p>0832WD</p> <p>chisel-shaped, 2.5 mm, bent</p>
<p>0832RD</p> <p>chisel-shaped, 5.0 mm, bent</p>	<p>0832GDLF</p> <p>angled face, 14 mm, 35°</p>	<p>0832LDLF</p> <p>angled face, 17 mm, 35°</p>	<p>0832MDLF</p> <p>angled face on both sides, 8 mm</p>
<p>0842UD/UDLF</p> <p>pencil point, 0.4 mm ϕ, extended</p>	<p>0842SD/SDLF</p> <p>pencil point, 0.8 mm ϕ, extended</p>	<p>0842BD/BDLF</p> <p>pencil point, 1.0 mm ϕ</p>	<p>0842YD/YDLF</p> <p>chisel-shaped, 1.6 mm</p>
<p>0842CD/CDLF</p> <p>chisel-shaped, 2.2 mm</p>	<p>0842KD/KDLF</p> <p>chisel-shaped, 2.2 mm, extended</p>	<p>0842ED/EDLF</p> <p>chisel-shaped, 3.2 mm</p>	<p>0842ID</p> <p>pencil point, 0.4 mm ϕ, bent</p>
<p>0842JD</p> <p>chisel-shaped, 2.2 mm, bent</p>			

Dimensions without pre-tinning