

Pitch: 5mm
 Rated voltage/current: 300V/15A
 Operation temperatures: -40°C to +105°C
 Withstand voltage: 2000V AC for 60s
 Insulation resistance: 500MΩ at 500V DC
 Wire range: 24 to 12AWG 2.5mm²
 Max. torque value: 0.4 Nm



Housing colour: Green
 Screw: Zinc-plated steel (A3)
 Wire cage: Nickel-plated brass or steel
 Pin Header: Tin-plated brass
 Wire stripping length: 5-6 ± 0.5mm
 Wave soldering: 260°C for 5s
 Hand soldering: 350°C for 10s

Order code	Poles
21-3930	2
21-3931	3

