



### Main

Range of product	Altivar
Range compatibility	Easy Altivar 610 Altivar Machine ATV340
Accessory / separate part category	Display and signalling accessories
Accessory / separate part type	Display terminal
Accessory / separate part destination	Variable speed drive
Product specific application	To control, adjust and configure the drive To display the current values To save and download configurations
IP degree of protection	IP21

### Complementary

User language	French German English Spanish Italian Chinese
Realtime clock	Without
Display type	Backlit LCD screen white
Messages display capacity	2 lines
Pixel resolution	128 x 64
Net weight	0.05 kg

### Environment

Ambient air temperature for operation	-15...50 °C
---------------------------------------	-------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	107.0 g
Package 1 Height	5.7 cm
Package 1 width	9.2 cm
Package 1 Length	12.4 cm
Unit Type of Package 2	S03
Number of Units in Package 2	45
Package 2 Weight	5.5 kg
Package 2 Height	30.0 cm
Package 2 width	30.0 cm
Package 2 Length	40.0 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------