


Inductive sensor

IEBC003BASKG/0,23M

**Product characteristics**

Electrical design		PNP/NPN
Output function		normally open
Sensing range [mm]		3
Housing		threaded type
Dimensions [mm]		M8 x 1 / L = 37

Electrical data

Operating voltage [V]		10...30 DC
Current consumption [mA]		< 10; (only in 3-wire operation)
Protection class		III
Reverse polarity protection		yes

Outputs

Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC [V]		2.8
Minimum load current [mA]		2; (only in 2-wire operation)
Max. leakage current [mA]		0.5; (only in 2-wire operation)
Permanent current rating of switching output DC [mA]		100
Switching frequency DC [Hz]		1000
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Sensing range [mm]		3
Operating distance [mm]		0...2.4

Accuracy / deviations

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3
Hysteresis [% of Sr]		1...15



Operating conditions

Ambient temperature [°C]		0...70
Protection		IP 67

Inductive sensor

IEBC003BASKG/0,23M

Tests / approvals		
EMC		EN 60947-5-2
MTTF [years]		3019
Mechanical data		
Weight [g]		22.2
Housing		threaded type
Mounting		flush mountable
Dimensions [mm]		M8 x 1 / L = 37
Thread designation		M8 x 1
Materials		brass white bronze coated; sensing face: LCP
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Accessories (supplied)		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 0.23 m, PVC; 3 x 0.14 mm ²		
Connection		



Core colours :

- BK = black
 BN = brown
 BU = blue