



Part no.: 50120538
TKS 40x60.1.AF
Reflector

Figure can vary

Contents

- Technical data

Part no.: 50120538 – TKS 40x60.1.AF – Reflector

Technical data

Special design

Special design	Anti-fog coating
----------------	------------------

Mechanical data

Design	Rectangular
Mounting dimension, width	40 mm
Reflection surface width	37 mm
Mounting dimension, height	60 mm
Reflection surface height	56 mm
Mounting dimension, thickness	7.2 mm
Triple reflector size	2.3 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Coating	Anti-fog
Net weight	12 g
Type of fastening	Adhesive Through-hole mounting

Environmental data

Ambient temperature, operation	-40 ... 65 °C
--------------------------------	---------------

Certifications

Degree of protection	IP 67
----------------------	-------

Classification

Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467