


G3VM-35□G□/351VY/401G□/401VY

MOS FET Relays SOP 4-pin, General-purpose Type

General-purpose MOS FET Relays in SOP 4-pin packages for a wide range of applications

- Contact form: 1a (SPST-NO) or 1b (SPST-NC)
- Load voltage: 350 V or 400 V



Note: The actual product is marked differently from the image shown here.

RoHS Compliant

Application Examples



- Semiconductor test equipment
- Test & Measurement equipment
- Communication equipment
- Various battery-driven devices
- Security equipment
- Industrial equipment
- Power circuit
- Amusement equipment

Package

(Unit : mm, Average)

SOP 4-pin

Special SOP 4-pin



Note: The actual product is marked differently from the image shown here.

Model Number Legend

G3VM-□□□□□
1 2 3 4 5

- 1. Load Voltage**
35 : 350 V
40 : 400 V
- 2. Contact form**
1 : 1a (SPST-NO)
3 : 1b (SPST-NC)

- 4. Additional functions**
None: Dielectric strength between I/O 1500 V
Y: Dielectric strength between I/O 3750 V

- 3. Package**
G : SOP 4-pin
V : Special SOP 4-pin

- 5. Other informations**
When specifications overlap, serial code is added in the recorded order.

Ordering Information

Package	Contact form	Terminals	Load voltage (peak value) *	Continuous load current (peak value) *	Stick packaging		Tape packaging	
					Model	Minimum package quantity	Model	Minimum package quantity
SOP4	1a (SPST-NO)	Surface-mounting Terminals	350 V	100 mA	G3VM-351G1	100 pcs.	G3VM-351G1(TR)	2,500 pcs.
Special SOP 4-PIN				G3VM-351G	G3VM-351G(TR)			
	1b (SPST-NC)			110 mA	G3VM-351VY	125 pcs.	G3VM-351VY(TR05)	500 pcs.
SOP4	1a (SPST-NO)		120 mA	G3VM-353G	100 pcs.	G3VM-353G(TR)	2,500 pcs.	
			100 mA	G3VM-401G1		G3VM-401G1(TR)		
Special SOP 4-PIN	1a (SPST-NO)		120 mA	G3VM-401G	125 pcs.	G3VM-401G(TR)	500 pcs.	
		110mA	G3VM-401VY	G3VM-401VY(TR05)				

* The AC peak and DC value are given for the load voltage and continuous load current.

Note: To order tape packaging for Relays with surface-mounting terminals, add "(TR)", "(TR05)" to the end of the model number.

SOP

G3VM-35□G□/351VY/401G□/401VY

Absolute Maximum Ratings (Ta = 25°C)


Item		Symbol	G3VM-351G1	G3VM-351G	G3VM-351VY	G3VM-353G	G3VM-401G1	G3VM-401G	G3VM-401VY	Unit	Measurement conditions	
Input	LED forward current	IF	50		30	50	30	50	30	mA		
	LED forward current reduction rate	$\Delta I_F/^\circ C$	-0.5		-0.3	-0.5	-0.3	-0.5	-0.3	mA/°C	Ta ≥ 25°C	
	LED reverse voltage	VR	5		6	5		6		V		
Connection temperature		TJ	125								°C	
Load voltage (AC peak/DC)		V _{OFF}	350			400					V	
Output	Continuous load current (AC peak/DC)	Io	100	110	120	100	120	110		mA		
	ON current reduction rate	$\Delta I_O/^\circ C$	-1.0	-1.1	-1.2	-1.0	-1.2	-1.1		mA/°C	Ta ≥ 25°C	
	Pulse ON current	I _{op}	300	330	360	300	360	330		mA	t=100 ms, Duty=1/10	
	Connection temperature	TJ	125								°C	
Dielectric strength between I/O *		V _{I-O}	1500		3750	1500			3750	V _{rms}	AC for 1 min	
Ambient operating temperature		Ta	-40 to +85		-40 to +110	-40 to +85			-40 to +110	°C	With no icing or condensation	
Ambient storage temperature		T _{stg}	-55 to +125									°C
Soldering temperature		-	260								°C	10 s

* The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

Electrical Characteristics (Ta = 25°C)

Item		Symbol	G3VM-351G1	G3VM-351G	G3VM-351VY	G3VM-353G	G3VM-401G1	G3VM-401G	G3VM-401VY	Unit	Measurement conditions	
Input	LED forward voltage	Minimum	1.0		1.1	1.0	1.1	1.0	1.1	V	I _F =10 mA	
		Typical	1.15		1.27	1.15	1.27	1.15	1.27			
		Maximum	1.3		1.4	1.3	1.4	1.3	1.4			
	Reverse current	I _R	Maximum						10		μA	V _R =5 V
	Capacitance between terminals	C _T	Typical		30						pF	V=0, f=1 MHz
	Trigger LED forward current	I _{FT} (I _{FC}) *2	Typical	0.4	1	0.8	1	-	1	0.8	mA	G3VM-351G1/351G/401G1 : I _o =100 mA G3VM-351VY/401VY : I _o =110 mA G3VM-353G : I _{OFF} =10 μA G3VM-401G : I _o =120 mA
Maximum			1	3			0.2	3				
Release LED forward current	I _{FC} (I _{FT}) *2	Minimum	0.1				-	0.1		mA	G3VM-351G1/351VY/351G/401G1/ 401G/401VY : I _{OFF} =100 μA G3VM-353G : I _o =120 mA	
		Typical	-		0.4	-	0.001	-	0.5			
Output	Maximum resistance with output ON	Typical	35 (25)		35 (22)	15	18	17	40 (30)	Ω	G3VM-351G1 : I _F =2 mA, I _o =100 mA Values in parentheses are for t < 1 s. G3VM-351G : I _F =5 mA, I _o =110 mA Values in parentheses are for t < 1 s. G3VM-351VY/401VY : I _F =5 mA, I _o =110 mA Values in parentheses are for t < 1 s. G3VM-353G : I _o =120 mA G3VM-401G1 : I _F =0.5 mA, I _o =100 mA, t < 1 s G3VM-401G : I _F =5 mA, I _o =120 mA	
		Maximum	50 (35)		25	35		65 (45)				
	Current leakage when the relay is open	I _{LEAK}	Typical	1	-	1	-	1	-	1	nA	G3VM-351G1/351VY/351G : V _{OFF} =350 V G3VM-353G : V _{OFF} =350 V, I _F =5 mA G3VM-401G1/401G/401VY : V _{OFF} =400 V
Capacitance between terminals	C _{OFF}	Typical	35	30	30	65	70		30	pF	G3VM-351G1/351VY/351G/401G1/ 401G/401VY : V=0, f=1 MHz G3VM-353G : V=0, f=1 MHz, I _F =5 mA	
Capacitance between I/O terminals	C _{I-O}	Typical	0.8						pF	f=1 MHz, V _S =0 V		
Insulation resistance between I/O terminals	R _{I-O}	Minimum	1000						MΩ	V _{I-O} =500 VDC, RoH≤60%		
		Typical	10 ⁸									
Turn-ON time	t _{ON}	Typical	1	0.3	0.5	-	2	0.3	0.5	ms	G3VM-351G1 : I _F =2 mA, R _L =200 Ω, V _{DD} =20 V G3VM-401G1 : I _F =0.5 mA, R _L =200 Ω, V _{DD} =20 V Others : I _F =5 mA, R _L =200 Ω, V _{DD} =20 V *1	
		Maximum	5	1			10	1				
Turn-OFF time	t _{OFF}	Typical	1	0.1		-	1	0.1		ms	G3VM-351G1 : I _F =2 mA, R _L =200 Ω, V _{DD} =20 V G3VM-401G1 : I _F =0.5 mA, R _L =200 Ω, V _{DD} =20 V Others : I _F =5 mA, R _L =200 Ω, V _{DD} =20 V *1	
		Maximum	3	1	0.5	3	5	1	0.5			

*1. Turn-ON and Turn-OFF Times



*2. These values are for Relays with NC contacts

Recommended Operating Conditions

For usage with high reliability, Recommended Operation Conditions is a measure that takes into account the derating of Absolute Maximum Ratings and Electrical Characteristics.

Each item on this list is an independent condition, so it is not simultaneously satisfy several conditions.

Item	Symbol		G3VM-351G1	G3VM-351G	G3VM-351VY	G3VM-353G	G3VM-401G1	G3VM-401G	G3VM-401VY	Unit	
Load voltage (AC peak/DC)	V _{DD}	Maximum	280				320				V
Operating LED forward current	I _F	Minimum	-			5		-		5	mA
		Typical	2	7.5		-	0.5	7.5			
		Maximum	25								
Continuous load current (AC peak/DC)	I _O	Maximum	80	100	110	120	80	120	110		
Ambient operating temperature	T _a	Minimum	-20								°C
		Maximum	65		100		65		100		

Spacing and Insulation


Item	G3VM-35□G□/401G□	G3VM-351VY/401VY	Unit
	Minimum		
Creepage distances	4.0	5.0	mm
Clearance distances	4.0	5.0	
Internal isolation thickness	0.1	0.2	

SOP


G3VM-35□G□/351VY/401G□/401VY

Engineering Data


LED forward current vs. Ambient temperature




Continuous load current vs. Ambient temperature




LED forward current vs. LED forward voltage




Continuous load current vs. On-state voltage




G3VM-351VY/401G/401G1/401VY




On-state resistance vs. Ambient temperature




G3VM-351VY/401G/401G1/401VY




Trigger LED forward current vs. Ambient temperature



Turn ON, Turn OFF time vs. LED forward current




G3VM-351VY/401G/401G1/401VY




Engineering Data


● Turn ON, Turn OFF time vs. Ambient temperature G3VM-351G/351G1/353G



G3VM-351VY/401G/401G1/401VY





● Current leakage vs. Ambient temperature G3VM-351G/351G1/353G/351VY/ 401G/401G1



● Current leakage vs. Load voltage

G3VM-401VY




■ Appearance / Terminal Arrangement / Internal Connections


● Appearance

SOP (Small Outline Package)

SOP 4-pin




Special SOP 4-pin (G3VM-351VY/401VY)




- Note 1:** The actual product is marked differently from the image shown here.
- Note 2:** "G3VM" does not appear in the model number on the Relay.
- Note 3:** The indentation in the corner diagonally opposite from the pin 1 mark is from a pin on the mold.

● Terminal Arrangement/Internal Connections (Top View)

G3VM-351G1/G/VY
G3VM-401G1/G/VY



G3VM-353G



■ Dimensions (Unit: mm)


SOP (Small Outline Package)

SOP 4-pin




Surface-mounting Terminals

Weight: 0.1 g




Actual Mounting Pad Dimensions

(Recommended Value, Top View)




Note: The actual product is marked differently from the image shown here.

Special SOP 4-pin * (G3VM-351VY/401VY)




Surface-mounting Terminals

Weight: 0.1 g



Actual Mounting Pad Dimensions

(Recommended Value, Top View)



* The external dimensions are different from those of the standard SOP 4-pin, but the mounting pad dimensions are the same.

Note: The actual product is marked differently from the image shown here.

■ Approved Standards

UL recognized

Model	Approved Standards	Contact form	File No.
G3VM-351G1 G3VM-351G G3VM-401G G3VM-351VY G3VM-401VY	UL (recognized)	1a (SPST-NO)	E80555
G3VM-353G		1b (SPST-NC)	

Models Certified by BSI for EN/IEC Standards

Model	Approved Standards	Contact form	File No.
G3VM-401G	EN62368-1 (BSI certified)	1a (SPST-NO)	VC669262

■Safety Precautions

- Refer to the *Common Precautions for All MOS FET Relays* for precautions that apply to all MOS FET Relays.

SOP

G3VM-35□G□/351VY/401G□/401VY

Please check each region's Terms & Conditions by region website.

OMRON Corporation

Electronic and Mechanical Components Company

Regional Contact

Americas

<https://www.components.omron.com/>

Asia-Pacific

<https://ecb.omron.com.sg/>

Korea

<https://www.omron-ecb.co.kr/>

Europe

<http://components.omron.eu/>

China

<https://www.ecb.omron.com.cn/>

Japan

<https://www.omron.co.jp/ecb/>