

3-jaw tapered rod lathe chuck DURO-T

Hand chuck in acc. with ISO 702-3



Application:

Optimised for turning applications, which require extremely high clamping forces, maximum concentricity and reliable continuous repeatability.

Execution:

- Grease nipples with very easy access are located at each jaw position.
- Fast and regular lubrication to ensure a long service life
- For short tapered bayonet fastening, DIN ISO 702-3 (DIN 55027)
- Large through-bore
- Chuck body surface hardened

Advantage:

- No longer necessary to dismantle the chuck before lubricating the guides.
- With visual jaw locking and jaw quick-change system

Delivery:

With 1 set of plain jaws and reverse top jaws, 1 spanner, 1 set of stud bolts and collar nuts (for short taper DIN ISO 702-3 (DIN 55027))



Art. no.	22428 246
Brand	RÖHM
Manufacturer Part Number	437548
Outer diameter	160 mm
DIN	55027
ISO	702-3
Taper shank size	5
Min./max. external clamping width	5-161 mm
Min./max. internal clamping width	67-174 mm
Drill hole 2	42 mm
Max. rotation speed	5400
Tapered bolt diameter	82.5 mm
Tension force	73 kN
Max. torque	120 Nm
Gross Weight	11.840 kg
Product Group	202

EAN

4019208227870