## **Moisture Barrier Bag**





#### **Features**

### RoHS Compliant

- · Protects electronics from moisture and static damage
- · Opaque and light tight ensuring the inside item can not been seen from outside
- · Firm lamination and hot sealing offers superior resistance of vapour and oxygen
- Surface resistance of 10<sup>8</sup>~10<sup>11</sup>Ω
- These bags are ideal for transporting and storing sensitive devices such as circuit boards and electronic components.
- · Available in 3.6 / 4.4 and 6Mil thicknesses
- · Flexible structure & easy to vacuum seal

#### Construction

Our moisture barrier bags are constructed in 3 layers. The bag features an anti static metallized polyester outer layer and an anti static inner layer. In between are layers of polyethylene, nylon and an aluminium foil shield.


#### Configuration(s)

Our bags are available in custom sizes or in several industry standard sizes. Bags are offered in a 3-seal configuration, with our standard flexographically printed artwork. Our bags can also be personalised with your company logo on any bespoke orders.

#### Standard Bag Artwork

Our moisture barrier bags are produced with the following sample artwork as standard. For further information on bespoke/printed orders, please contact one of our sales team. Please note there is a MOQ of 20,000 bags on all printed bags.

Note: All of our moisture barrier bags are batch coded for QC traceability.







#### **Test Conditions**

The following results were taken under the following environmental test conditions: Temperature: 21.3°C / Humidity: 45.1%

Item	Test Standard	Result
Film Composition	N/A	PET-AL/NY/CPE
Metal Layer Resistance	ASTMD-257	<0.1Ω
Inner and Outer Resistance	ASTMD-257	10 <sup>8</sup> - 10 <sup>11</sup> Ω
Static Shielding - Capacitance Probe	EIA541 (Voltage Difference)	<10V
Moisture Vapour Transmission (at 90%RH, 23°C)	ASTMF1249-2005	0.02 gm/100sq.in/24hrs
Tensile Strength	ASTM D882	MD/TD >24lbs/in

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



# **Moisture Barrier Bag**



Item	Test Standard	Result
Puncture Resistance	ASTM F1306-90(2002)	Inner to Outer: 54.7N Outer to Inner: 51.3N
Tear Strength	ASTM D1004	MD >3lbs/in TD >3.8lbs/in
Heat Seal Temperature	-	250-375°F
Heat Seal Time	-	0.5-3.5 sec
Heat Seal Pressure	-	30-70 PSI
Seal Strength	GB/96-04-10	>3kg/cm
Contact Corrosivety	FTMS 101C Method 3005	No visible spots detected
Static Decay Time	IEC61340-5-1 (±1000 - ±100V)	≤2S

#### **Test Conclusion**

The shielding bag is tested accordance with the relevant test standard & requirements.

Test Item:	Test Method:	Measured Equipment(s):	MDL:
Lead (Pb)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Cadmium (Cd)	IEC 62321:2008 Ed.1 Sec.8	ICP-OES	2mg/kg
Mercury (Hg)	IEC 62321:2008 Ed.1 Sec.7	ICP-OES	2mg/kg
Hexavalent Chromium (Cr(VI))	IEC 62321:2008 Ed.1 Annex C	UV-Vis	2mg/kg
Polybrominated Biphenyls (PBBs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg
Polybrominated Diphenyl Ethers (PBDEs)	IEC 62321:2008 Ed.1 Annex A	GC-MS	5mg/kg

EMI Shielding: Meets required range of EN 61340-5-1 tested per IEC 61340-2-3 and ANSI/ESD STM11.31

#### **Part Number Table**

Description	Part Number
Moisture Barrier Bag 3.6Mil / 92 microns, 254mm×304.8mm, PK100	MC0180132

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

