

148354-1 ✓ ACTIVE

EUROCARD


TE Internal #: 148354-1

Rack & Panel Contacts, Pin, Contact Length 17.6 mm [.693 in], Gold, Cable-to-Board, Printed Circuit Board, 3A Contact Current Rating (Max), Power

[View on TE.com >](#)



Connectors > PCB Connectors > Backplane Connectors > Rack & Panel Backplane > Rack & Panel Contacts



Contact Type: Pin

Contact Length: 17.6 mm [.693 in]

Contact Mating Area Plating Material: Gold

Connector System: Cable-to-Board

Connector & Contact Terminates To: Printed Circuit Board

### Features

#### Product Type Features

DIN Level	II
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

#### Contact Features

Contact Mating Area Plating Material Thickness	.76 µm
Contact Orientation	Right Angle
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Brass
Contact Type	Pin
Contact Length	17.6 mm [.693 in]
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	3 A

#### Termination Features

Termination Method to Printed Circuit Board	Through Hole - Solder
---	-----------------------

#### Mechanical Attachment

Contact Retention Type Within Housing	Snap-In
---------------------------------------	---------

#### Usage Conditions



Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

### Operation/Application

Circuit Application	Power
---------------------	-------

### Packaging Features

Packaging Method	Tray
------------------	------

### Other

Comment	For Use With Type M Connector
---------	-------------------------------

## Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (13% in Component Part) <b>Article Safe Usage Statements:</b> Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

## Customers Also Bought



TE Part #1926017-1  
PIN Connector Straight Solder Tails



TE Part #6-1546700-5  
JC6-Q308-04=JC6 ASSEMBLY Matte Tin Pl



TE Part #6-534204-4  
72 MODU 2-PC CE RECP ASSY, RoHS




TE Part #2180640-1  
SFP+ Stacked Cage Assemblies



TE Part #2018855-1  
ASSY, SEATING TL, 4 ROW, 8 COL



TE Part #2170207-4  
1X6 QSFP ASSEMBLY THRU BZL W/4 PORT LP




TE Part #3-1532018-4  
095-0087-8008=MCEM1-184LZ



TE Part #EG2927-000  
55A4122-20-2/9-9



TE Part #6-534978-0  
72 MODII 2PC HDR DR W/HLDWN, ROHS



TE Part #6651646-1  
CONNECTOR, PIN, RIGHT ANGLE, SOLDER, FLAT

## Documents

### Product Drawings

#### IEC-C M.POWER CONTACTS

English

### CAD Files

#### Customer View Model

[ENG\\_CVM\\_148354-1\\_C.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_148354-1\\_C.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_148354-1\\_C.3d\\_stp.zip](#)

English

### 3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

## Product Specifications



## Application Specification

English