

Type ER precision collet chuck sets

GERC HPD, DIN 6499/ISO 15488-B, sealed for internal coolant supply, concentricity of 2 µm

FAHRION®
FAR BEYOND PRECISION

Application:

For HSC machining with high precision machining results

Execution:

- HPD with seal for internal coolant supply (can be used up to 60 bar).
- With small concentricity and repeat tolerance 2 µm (for system tolerance 3 µm and with 3 x dia. maximum = 50 mm), clamp bridge h10.
- Surface super-finished for enhanced retention force.
- Only the nominal dimension can be clamped (straight shank with h8).
- Surface super-finished for enhanced retention force.
- With FAHRION | Protect corrosion protection for longer service life.

Advantage:

- Greater concentricity extends tool service life.
- Collets do not need to be replaced as often or can be used longer for specific applications.

Delivery:

1x type ER precision collet chuck set.



Art. no.	23323 659
Brand	FAHRION
Manufacturer Part Number	13626160080
Collet type	469E GERC32-HPD
Min./max. clamping range	4-20 mm
Outer diameter	33 mm
Length	40 mm
Coolant supply	Internal axial
Clamping bypass	-0.5 mm
Number of pieces in assortment/set	8
Gross Weight	1.548 kg
Product Group	235

EAN

4054631171161