

Technical Data Sheet Infrared MIDLED LED

IR89-01C/1R

Features

- Low forward voltage.
- View angle 30°(Typ.)
- Pb free
- The product itself will remain within RoHS compliant version.
- Compatible with infrared and vapor phase reflow solder process.
- IR89-01C/1R : Taping as Top view.



Descriptions

• IR89-01C/1R is an infrared emitting diode with miniature MIDLED package. The device is spectrally matched with silicon photodiode and phototransistor.

Applications

• Infrared applied system

Device Selection Guide

Revision

I ED Dont No	Chip	Long Color	
LED Part No.	Material	Lens Color	
IR89-01C/1R	GaAlAs	Water clear	

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 1 Page: 1 of 9


Device No: DIR-0000607 Prepared date: 12-16-2011 Prepared by: JAINE TSAI : 1

Release Date:2012-05-02 22:42:23.0

LifecyclePhase: **Expired Period: Forever**



Package Dimensions



Notes: 1.All dimensions are in millimeters

2.Tolerances unless dimensions ±0.1mm

Everlight Electronics Co., Ltd.

http://www.everlight.com

Rev 1

Page: 2 of 9

Device No: DIR-0000607

3.0

Prepared date: 12-16-2011

Prepared by: JAINE TSAI

正式發行 Approved

Expired Period: Forever

Release Date:2012-05-02 22:42:23.0

LifecyclePhase:



Absolute Maximum Ratings (Ta=25)

Parameter		Symbol	Rating	Units
Continuous Forward Current		I_{F}	65	mA
Peak Forward Current *	1	I_{FP}	500	mA
Reverse Voltage		V_R	5	V
Operating Temperature		T_{opr}	-40~ +85	
Storage Temperature		T_{stg}	-40 ~ +100	
Soldering Temperature	*2	T_{sol}	260	
Power Dissipation at(or below)25 Free	Air Temperature	P_d	100	mW

Notes: *1: I_{FP} Conditions--Pulse Width 500 μ s and Duty 5%.

Electro-Optical Characteristics (Ta=25)

Parameter	Symbol	Condition	Min.	Typ.	Max.	Unit
		I _F =20mA		12	-4	
Radiant Intensity	I_{E}	$I_F\!\!=\!\!100mA$ Pulse Width 100 μ s ,Duty 1%	16	55	125	mW/sr
Peak Wavelength	p	I _F =30mA	920	940	960	nm
Spectral Bandwidth		I _F =30mA		30		nm
		I _F =20mA		1.3	1.6	
Forward Voltage	V_{F}	$I_F\!\!=\!\!100mA$ Pulse Width 100 μ s ,Duty 1%		1.5	2.0	V
Reverse Current	I_R	$V_R=5V$			10	μA
Rise time	tr	I _F =150mA		15		ns
Fall time	tf	I _F =150mA		15		ns
View Angle	2 1/2	I _F =20mA		30		deg
Dimensions of the active chip area	L*W		(0.18*0.1	8	mm*mm
Chip Size	L*W			0.2*0.2	-	mm*mm

Condition: I_F=100mA

Unit: mW/sr

Bin Number	A	В	C	D
Min	16	25	40	63
Max	32	50	80	125

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 1 Page: 3 of 9

Device No: DIR-0000607 Prepared date: 12-16-2011 Prepared by: JAINE TSAI Revision Release Date:2012-05-02 22:42:23.0 : 1

正式發行 Approved LifecyclePhase:

Expired Period: Forever

^{*2:}Soldering time 5 seconds.



Typical Electro-Optical Characteristics Curves

Fig.1 Forward Current vs.

Ambient Temperature




Fig.2 Spectral Distribution




Fig.3 Relative Intensity vs

Forward Current





Fig.4 Relative Radiant Intensity vs.

Angular Displacement



Everlight Electronics Co., Ltd.

Device No: DIR-0000607

Revision : 1 LifecyclePhase: 正式發行 http://www.everlight.com

Rev 1

Page: 4 of 9

Prepared date: 12-16-2011

Prepared by: JAINE TSAI

Release Date:2012-05-02 22:42:23.0

Expired Period: Forever



1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).

- 2. Storage
- 2.1 Do not open moisture proof bag before devices are ready to use.
- 2.2 Shelf life in sealed bag from the bag seal date:

18 months at $10^{\circ}\text{C}\sim30^{\circ}\text{C}$ and < 90% RH.

- 2.3 After opening the package, the devices must be stored at $10^{\circ}\text{C} \sim 30^{\circ}\text{C}$ and $\leq 60\%$ RH, and used within 72 hours(floor life).
- 2.4 If the moisture absorbent material(desiccant material) has faded or unopened bag has exceeded the shelf life or devices(out of bag) have exceeded the floor life, baking treatment is required.
- 2.5 If baking is required, refer to IPC/JEDEC J-STD-033 for bake procedure or recommend the following conditions :

192 hours at $40^{\circ}\text{C} + 5/-0^{\circ}\text{C}$ and < 5 % RH (reeled/tubed/loose units) or

96 hours at $60^{\circ}\text{C} \pm 5^{\circ}\text{C}$ and < 5 % RH (reeled/tubed/loose units) or

24 hours at 125°C ± 5°C, not suitable for reel or tubes.

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 1 Page: 5 of 9

Device No: DIR-0000607 Prepared date: 12-16-2011 Prepared by: JAINE TSAI **Revision**: 1 Release Date: 2012-05-02 22:42:23.0


Se: Approved Expired Period: Forever

LifecyclePhase: Approve



3. Soldering Condition

3.1 Pb-free solder temperature profile



- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

Everlight Electronics Co., Ltd.

Device No: DIR-0000607

Revision: 1

LifecyclePhase: 正式發行 Approved http://www.everlight.com

Rev 1

Page: 6 of 9

Prepared date: 12-16-2011

Prepared by: JAINE TSAI

Expired Period: Forever

Release Date:2012-05-02 22:42:23.0




4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350 for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



Everlight Electronics Co., Ltd. http://www.everlight.com Rev 1 Page: 7 of 9

Device No: DIR-0000607 Prepared date: 12-16-2011 Prepared by: JAINE TSAI


Release Date: 2012-05-02 22:42:23.0

Approved Expired Period: Forever

Revision : 1 LifecyclePhase:




Package Dimensions



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

2. Carrier Tape Dimensions:(Quantity: 2000pcs/reel)



Note: The tolerances unless mentioned is ± 0.1 mm, Unit = mm

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 1 Page: 8 of 9


Device No: DIR-0000607 Prepared date: 12-16-2011 Prepared by: JAINE TSAI **Revision**: 1 Release Date: 2012-05-02 22:42:23.0

LifecyclePhase: Expired Period: Forever Expired Period: Forever



Packing Procedure

IR89-01C/1R



Label Form Specification



CPN: Customer's Production Number

P/N : Production Number QTY: Packing Quantity

CAT: Ranks

HUE: Peak Wavelength

REF: Reference

LOT No: Lot Number

MADE IN TAIWAN: Production Place

Notes

- 1. In case of changes the rules described in EVERLIGHT's document: PRO-016 "Control Procedure of engineering change" edition date 2007-11-06 will be followed.
- 2. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- These specification sheets include materials protected under copyright of EVERLIGHT corporation. Please don't reproduce or cause anyone to reproduce them without EVERLIGHT's consent.

EVERLIGHT ELECTRONICS CO., LTD.

Office: No 6-8,Zhonghua Rd., Shulin Dist., New Taipei City 23860, Taiwan, R.O.C Tel: 886-2-2685-6688 Fax: 886-2-2685-6897 http://www.everlight.com

Everlight Electronics Co., Ltd. http://www.everlight.com Rev 1 Page: 9 of 9

Device No: DIR-0000607 Prepared date: 12-16-2011 Prepared by: JAINE TSAI **Revision**: 1 Release Date: 2012-05-02 22:42:23.0

LifecyclePhase: Approved Expired Period: Forever