

Dimensions: [mm]












Scale - 6:1

Product Marking:

| Start of Winding | • |
|------------------|-----------------------|
| Marking | R56 (Inductance Code) |

Recommended Land Pattern: [mm]



No vias and traces in restricted area.

Scale - 6:1


Electrical Properties:

| Properties | | Test conditions | Value | Unit | Tol. |
|-------------------------|------------------|---------------------------|-------|------|------|
| Inductance | L | 100 kHz/ 10 mA | 0.56 | μΗ | ±20% |
| Rated Current | I _R | $\Delta T = 40 \text{ K}$ | 8.2 | А | max. |
| Saturation Current | I _{SAT} | IΔL/LI < 20 % | 9.55 | А | typ. |
| DC Resistance | R _{DC} | @ 20 °C | 7.5 | mΩ | typ. |
| DC Resistance | R _{DC} | @ 20 °C | 8.6 | mΩ | max. |
| Self Resonant Frequency | f _{res} | | 72 | MHz | typ. |

Certification:

| RoHS Approval | Compliant [2011/65/EU&2015/863] |
|----------------|---------------------------------------|
| REACh Approval | Conform or declared [(EC)1907/2006] |
| Halogen Free | Conform [JEDEC JS709B] |
| Halogen Free | Conform [IEC 61249-2-21] |

Schematic:



General Properties:

REVISION

DATE (YYYY-MM-DD)

It is recommended that the temperature of the component does not exceed +150°C under worst case conditions

| Ambient Temperature (referring to I _R) | -55 up to +110 °C | | | | | |
|--|--------------------|--|--|--|--|--|
| Operating Temperature | -55 up to +150 °C | | | | | |
| Storage Conditions (in original packaging) | < 40 °C; < 75 % RH | | | | | |
| Moisture Sensitivity Level (MSL) | 1 | | | | | |
| Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently | | | | | | |

ROHS REACT HALOGEN CHECKED

CHECKED

Dde

DESCRIPTION

DE




Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany Tel. +49 (0) 79 42 945 - 0

Germany
Tel. +49 (0) 79 42 945 - (
www.we-online.com
eiSos@we-online.com


| Dig | Dig


GENERAL TOLERANCE

Typical Inductance vs. Current Characteristics:





Typical Temperature Rise vs. Current Characteristics:







Typical Impedance Characteristics:






Packaging Specification - Tape and Reel: [mm]







Packaging is referred to the international standard IEC 60286 -3:2013

| | Таре Туре | A0 (mm) | B0 (mm) | W (mm) | T (mm) | T1 (mm) | T2 (mm) | K0 (mm) | P0 (mm) | P1 (mm) | P2 (mm) | DO (mm) | E1 (mm) | E2 (mm) | F (mm) | Material | Qty. (pcs.) |
|-----|-----------|------------|------------|------------|-----------|------------|------------|------------|------------|------------|------------|------------|------------|------------|-----------|-------------|----------------|
| I | | typ. | typ. | +0,3/ -0,1 | ref. | max. | typ. | typ. | ±0,1 | ±0,1 | ±0,05 | +0,1/-0,0 | $\pm 0,1$ | min. | ±0,05 | | |
| - [| 2a | 4,60 | 4,60 | 12,00 | 0,30 | 0,10 | 2,50 | 2,30 | 4,00 | 8,00 | 2,00 | 1,50 | 1,75 | 10,25 | 5,50 | Polystyrene | 1000 |





| A (mm) | B (mm) | C (mm) | D (mm) | N (mm) | W1 (mm) | W2 (mm) | W3 (mm) | W3 (mm) | Material |
|-----------|-----------|-----------|-----------|-----------|------------|------------|------------|------------|---------------------------|
| ± 2,0 | min. | min. | min. | min. | + 2,0 | max. | min. | max. | |
| 178,00 | 1,50 | 12,80 | 20,20 | 50,00 | 12,40 | 18,40 | 11,90 | 15,40 | Polystyrene/ Polyurethane |



Pull-of force Tape width 12 mm 0,1 N - 1,3 N



Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany

CHECKED

Dde

REVISION

Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com


PROJECTION METHOD 001.000 2019-09-06 DIN ISO 2768-1m **WE-MAPI SMT Power Inductor** ORDER CODE

DATE (YYYY-MM-DD)

744383560056HT SIZE/TYPE BUSINESS UNIT STATUS PAGE 4020 eiSos Valid 4/7

GENERAL TOLERANCE

Classification Reflow Profile for SMT components:



Classification Reflow Soldering Profile:

| Profile Feature | | Value |
|---|--------------------|-------------------|
| Preheat Temperature Min | T _{s min} | 150 °C |
| Preheat Temperature Max | T _{s max} | 200 °C |
| Preheat Time t_s from $T_{s min}$ to $T_{s max}$ | t _s | 60 - 120 seconds |
| Ramp-up Rate (T _L to T _P) | | 3 °C/ second max. |
| Liquidous Temperature | T _L | 217 °C |
| Time t _L maintained above T _L | t _L | 60 - 150 seconds |
| Peak package body temperature | T _p | see table below |
| Time within 5°C of actual peak temperaure | t _p | 20 - 30 seconds |
| Ramp-down Rate (T _L to T _P) | | 6 °C/ second max. |
| Time 25°C to peak temperature | | 8 minutes max. |

refer to IPC/ JEDEC J-STD-020E

Package Classification Reflow Temperature:

| | Properties | Volume mm³ <350 | Volume mm ³ 350-2000 | Volume mm³ >2000 |
|---|--|--------------------|------------------------------------|------------------|
| | PB-Free Assembly Package Thickness < 1.6 mm | 260 °C | 260 °C | 260 °C |
| I | PB-Free Assembly I Package Thickness 1.6 mm - 2.5 mm | 260 °C | 250 °C | 245 °C |
| | PB-Free Assembly I Package Thickness ≥ 2.5 mm | 250 °C | 245 °C | 245 °C |

refer to IPC/ JEDEC J-STD-020E

| 3 9 8 | | CHECKED Dde | REVISION 001.000 | DATE (YYYY-MM-DD) 2019-09-06 | GENERAL TOLERANCE DIN ISO 2768-1m | | PROJECTION METHOD | — |
|-----------------------------------|---|-------------------|------------------|---------------------------------|-----------------------------------|-----------------|-------------------|-------------|
| ROHS REACH HALOGEN COMPLIANT PREE | | WE-MA | API SMT | Power Inc | ductor | | | |
| | Wirth Elektronik elSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany | | | | | 7443 | 83560056H | Т |
| WÜRTH ELEKTRONIK | Tel. +49 (0) 79 42 945 - 0 | SIZE/TYPE 4020 | | | BUSINESS UNIT eiSos | status Valid | | PAGE 5/7 |

Cautions and Warnings:

The following conditions apply to all goods within the product series of WE-MAPI of Würth Elektronik eiSos GmbH & Co. KG:

General:

- This electronic component was designed and manufactured for use in general electronic equipment.
- Würth Elektronik must be asked for written approval (following the PPAP procedure) before incorporating the components into any
 equipment in fields such as military, aerospace, aviation, nuclear control, submarine, transportation (automotive control, train control,
 ship control), transportation signal, disaster prevention, medical, public information network, etc. where higher safety and reliability are
 especially required and/or if there is the possibility of direct damage or human injury.
- Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheet specified values. If the usage and operation conditions
 specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged.
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
 Elektronik does not guarantee any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
 sustainability over time.
- The customer is responsible for the functionality of their own products. All technical specifications for standard products also apply to customer specific products.

Product specific:

Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- All other soldering methods are at the customers' own risk.
- To improve the solderability of bottom termination components please refer to appnote ANPO36 on our homepage

Cleaning and Washing:

Washing agents used during the production to clean the customer application may damage or change the characteristics of the wire
insulation, marking or plating. Washing agents may have a negative effect on the long-term functionality of the product.

Potting:

If the product is potted in the costumer application, the potting material may shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the core. Expansion could damage the components. We recommend a
manual inspection after potting to avoid these effects.


Storage Conditions:

- A storage of Würth Electronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer
 degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of
 shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.

Handling:

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- · Applying currents with audio-frequency signals may result in audible noise due to the magnetostrictive material properties.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.



Important Notes

The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

