


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0768671012](#)
Status: **Active**
Overview: [iPass+ HD Interconnect System](#)
Description: [iPass+ HD Internal Cable and Connector Assembly, 1x2 , 0.76µm, Lead-Free](#)

Documents:

3D Model	Packaging Specification PK-76867-001 (PDF)
Drawing (PDF)	Test Summary TS-76866-1004-001 (PDF)
Product Specification PS-76867-001-001 (PDF)	Test Summary TS-76867-001-001 (PDF)
Application Specification AS-76867-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-76867-002-001 (PDF)	



Agency Certification

CSA	LR19980
UL	E107635

General

Product Family	I/O Connectors
Series	76867
Application	Wire-to-Board
Component Type	Internal Receptacles
Electrical Model	Yes
Overview	iPass+ HD Interconnect System
Product Name	iPass+
Type	N/A
UPC	887191049229

Physical

Circuits (Loaded)	72
Circuits (maximum)	72
Color - Resin	Black
Durability (mating cycles max)	250
Flammability	94V-0
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	8.145/g
Number of Rows	1
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.37mm
Packaging Type	Tray
Panel Mount	No
Pitch - Mating Interface	0.75mm
Pitch - Termination Interface	0.75mm
Plating min - Mating	0.762µm, 1.524µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Temperature Range - Operating	-40° to +80°C
Termination Interface: Style	Through Hole - Compliant Pin

Electrical

Current - Maximum per Contact	1.0A
-------------------------------	------

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[76867 Series](#)

Mates With

[100189](#) , [100171](#) , [100190](#) , [100219](#) ,
[100172](#) , [100220](#) , [100221](#) , [100222](#) ,
[100223](#) , [100224](#) , [100225](#) , [100226](#)

Voltage - Maximum 30V AC (RMS)/DC

Solder Process Data

Lead-free Process Capability N/A

Material Info

Reference - Drawing Numbers

Application Specification AS-76867-001-001, AS-76867-002-001

Electrical Model Document EE-76866-1004

Packaging Specification PK-76867-001

Product Specification PS-76867-001-001

S-Parameter Model SP-76866-001, SP-76866-100, SP-76866-1004

Sales Drawing SD-76867-1000-001

Test Summary TS-76866-1004-001, TS-76867-001-001

This document was generated on 07/19/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION