



Figure similar

COMMUTATING CHOKE FOR CONVERTER;  
 PHASES:3; UN1(V):400; ITHMAX 1(A) / F1(HZ):25 /50;  
 I LN (A):22,5; UK(%):4; LN(MH):0,889; TA/ISOKL:40 /B;  
 IP00; TYPE OF TERMINALS:SCREW CONNECTION;  
 EN 61558-2-20 >CHOKE<(><<>>

### General technical data:

<b>Product designation</b>		Kommut.-Drossel f. Stromrichter
<b>product brand name</b>		SIDAC
<b>Phase number</b>		3
<b>Type of voltage</b>		AC
<b>Operating voltage Rated value</b>	V	400
<b>Operating frequency Rated value</b>	Hz	50
<b>Current</b>		
• with AC		
— Rated value	A	22.5
— maximum	A	25
• for DC Rated value	A	30.6
<b>Peak current</b>	A	31
<b>Inductivity Rated value</b>	H	0.00089
<b>Relative inductive drop in voltage on the measurement level current, voltage and frequency</b>	%	4
<b>Active power loss of the coil</b>	W	53
<b>Active power loss of the iron core</b>	W	9

### Mechanical data:

<b>Type of electrical connection for main current circuit</b>		screw-type terminals
<b>Width</b>	m	0.178
<b>Height</b>	m	0.153
<b>Depth</b>	m	0.105

### Ambient conditions:

<b>Thermal class acc. to IEC 60085</b>		B
--	--	---

Ambient temperature Rated value	°C	40
Protection class IP		IP00

#### Certificates/ approvals:

##### Declaration of Conformity



EG-Konf.

#### Further information

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

##### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

##### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=4EP37015DS00>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/4EP37015DS00>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=4EP37015DS00&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=4EP37015DS00&lang=en)

last modified:

16.03.2015