

# Customer Information Sheet

DRAWING No.: D01-992XXXX

SHEET 2 OF 2


IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



**SPECIFICATION:**

**MATERIAL:**  
MOULDING

~~01 = 30% G.F. POLYESTER UL94V-0, BLACK~~  
46 = POLYAMIDE 46 UL94V-0, BLACK

CONTACT = BRASS

**FINISH:**

CONTACT = 3.5-5.0µ 100% TIN OVER 2µ NICKEL

**ELECTRICAL:**

CURRENT RATING AT 25°C = 1.5A

CURRENT RATING AT 85°C = 0.25A

CONTACT RESISTANCE:

INITIAL = 15 mΩ MAX

AFTER CONDITIONING = 23 mΩ MAX

INSULATION RESISTANCE:

INITIAL = 1,000 MΩ MIN

AFTER CONDITIONING = 100 MΩ MIN

**MECHANICAL:**

DURABILITY = 1,000 OPERATIONS

**ENVIRONMENTAL:**

TEMPERATURE RANGE = -55°C TO +125°C

**PACKING:**

BAG

FOR COMPLETE SPECIFICATION, SEE COMPONENT SPECIFICATION C004XX (LATEST ISSUE)

PART No.	No. OF CONTACTS	DIM 'A'	DIM 'B'
D01-99220XX	20	51.10-50.70	(48.26)
D01-99232XX	32	81.10-81.60	(78.74)

**NOTES:**

1. RECOMMENDED PCB HOLE SIZE = Ø0.80mm MIN.

**OBSELETE**

ORDER CODE:

**D01-992XXXX**

No. OF CONTACTS  
20, 32

FINISH

~~01 = TIN~~

46 = 100% TIN

RA	9	14.01.09	10257
NAME	ISS.	DATE	C/NOTE
APPROVED:		R. ADDE	
CHECKED:		M.G. PLESTED	
DRAWN:		D. FAIRS	
CUSTOMER REF.:			
ASSEMBLY DRG.:			

**HARWIN**

HARWIN USA  
TEL: 603 893 5376  
FAX: 603 893 5396  
mis@harwin.com

HARWIN Europe (UK)  
TEL: 023 9231 4545  
FAX: 023 9231 4590  
mis@harwin.co.uk

HARWIN Asia  
TEL: +65 6 779 4909  
FAX: +65 6 779 3868  
mis@harwin.com.sg

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

**TOLERANCES**  
X. = ±1mm  
X.X = ±0.25mm  
X.XX = ±0.10mm  
X.XXX = ±0.01mm  
**ANGLES = ±5°**  
**UNLESS STATED**

**MATERIAL:**  
SEE ABOVE  
**FINISH:** SEE ABOVE  
**S/AREA:** mm<sup>2</sup>

**TITLE:**  
I.C. SIL THROUGH HEADER  
**DRAWING NUMBER:**  
**D01-992XXXX**

SHT  
2 OF 2