

# M 320 / M 320FB / P 310 series specifications

The M 320/ M 320FB/ P310 series offers the solution that is right for your needs, whether it's just easy-to-manage and compact printing, or multifunction productivity. Compact footprints make these solutions ideal for smaller spaces and maintenance and management are simple, with intuitive operation.

## Features for printers in this series include:

- Crisp 32 pages per minute output
- P 310 is ideal for use on desktops or under counters
- M 320 provides printing, scanning and copying
- M 320FB comes with 4.3 inch touch panel and ARDF
- Best in class security including SNMPv3-encrypted communications for device monitoring, secure email transmissions by SMTP over SSL/TLS

## M 320 / M 320FB / P 310

### MAIN SPECIFICATIONS

GENERAL	M 320	M 320FB	P 310
Varm-up time	30 seconds	30 seconds	26 seconds
First output speed: B/W		7.1 seconds	20 00001140
Continuous output speed		32 ppm	
Nemory: standard	256 MB	256 MB	128 MB
Veight	18 kg	18 kg	13 kg
Dimensions: W x D x H	405 x 392 x 407 mm	405 x 392 x 420 mm	370 x 392 x 262 mm
ower source aser classification	220 - 240 V, 50 - 60 Hz	220 - 240 V, 50 - 60 Hz Class 1 Laser Product (IEC60825 - 1:2014)	220 - 240 V, 50 - 60 Hz
COPIER			
Multiple copying	-	Up to 99 copies	-
Resolution	-	1,200 x 1,200 dpi	-
loom	-	From 25% to 400% in 1% steps	-
PRINTER			
Printer language: standard	PCL5e (MAC), PCL6 (Windows & Linux), PostScript3 (Windows)		
Print resolution: maximum	1,200 x 1,200 dpi		
letwork interface: standard	Ethernet 10 base-T/100 base-TX, USB2.0 Type B		
Network interface: option	Wireless LAN (IEEE 802.11 ab/gh/ac)		
Vindows® environments	Windows® 8.1, Windows® 10, Windows® Server 2012, Windows® Server 2012R2, Windows® Server 2016, Windows® Server 2019		
Mac OS environments	2019 Macintosh OS X v10.10 or later		
Other supported environments	Linux environment		
SCANNER			
Scanning: B/W	13 ipm	13 ipm	
-	4.5 ipm	•	-
Scanning: full colour Resolution: maximum		4.5 ipm	-
Resolution. maximum	600 dpi	600 dpi	-
AX			
Compatibility		ITU-T (CCITT) G3	-
ransmission speed	-	3 seconds	-
Nodem speed: maximum	-	33.6 Kbps	-
PAPER HANDLING			
Recommended paper size	Standard paper tray(s): (A4, A5, A6, B5, B6)		
Paper input: standard	300 sheets		
Paper input: maximum		550 sheets	
	50 -hh-		105
Paper output: standard Paper weight	50 sheets	50 sheets 52 - 162 g/m²	125 sheets
ECOLOGY		Ŭ	
Power consumption: operation	514 W	520 W	512 W
Power consumption: sleep	0.87 W	0.87 W	0.72 W
FEC*	0.423 kWh/week	0.423 kWh/week	0.408 kWh/week
		U.TLU NVIJWCCN	0.700 KVVIJWCCK
OUTPUT TRAYS AND FINISHER	OPTIONS		

#### CONSUMABLES

Starter toner	1,000 prints
Toner (regular yield)	3,500 prints
( . ) )	- ( ) - F =
Toner (high yield)	7,000 prints
	· ;
Consumable vield measuring	

ıg method ISO/IEC 19752

ISO9001 certified, ISO14001 certified, ISO27001 certified

COMMISSION REGULATION (EU) 2019/2020. The light source of this product is not intended for applications other than image printing.

Ricoh Europe (Netherlands) B.V. "Nieuw Kronenburg" Prof.

W.H. Keesomlaan 1 1183 DJ Amstelveen The Netherlands





All brand and/or product names are trademarks of their respective owners. Specifications and external appearance are subject to change without notice. The colour of the actual product may vary from the colour shown in the brochure. The images in this brochure are not real photographs and slight diff Copyright © 2021 Ricoh Europe PLC. All rights reserved. This brochure, its contents and/or layout may not be modified and/or adapted, copied in part or in whole and/or incorporated into other works without the prior written permission of Ricoh Europe PLC.



Apple AirPrint

ricoh-europe.com