

ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

SPC-F005.DWG

	564	1
DUCED	DCP	#

REV

RELEASED 564 Α 1892 В UPDATE TO ROHS COMPLIANT

REVISIONS


DESCRIPTION

DOC. NO. SPC-F005 * Effective: 7/8/02 * DCP No: 1398 DRAWN DATE CHECKD DATE APPRVD 3/24/00

HYO

ΕO

DATE JC 10/6/00 DJC 10/9/00 03/15/06 3/15/06 НО 3/15/ НΟ



Specifications:

- 1- Wire: 26 AWG, 1007 UL/CSA Approved
- 2- Contacts: Brass, nickel plated, mounted on

0.012 [0.30] Min. thickness PVC & .032[0.81] thick fiber insulation.

- 3- Red wire connected to female contact
- 4- Black wire connected to male contact.

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED
HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE
BELIEVE TO BE ACCURATE AND RELIABLE. SINCE
CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE
USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT
FOR THE INTENDED USE AND ASSUME ALL RISK AND
LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:		
UNLESS OTHERWISE	ı	
SPECIFIED		
DECIMAL		
$.XXX \pm 0.015 [0.38]$		

DRAWN BY:	DATE:	
HISHAM ODISH	3/24/00	
CHECKED BY:	DATE:	
JOHN COLE	10/6/00	
APPROVED BY:	DATE:	
DANIEL CAREY	10/9/00	

	DRAW	ING TITLE:				
0	ECONOMY 9 VOLT BATTERY STRAP					
	SIZE	DWG. NO.		ELEC	TRONIC FILE	REV
0	Α	8459	-0673	16N941.DWG		В
0	SCAL	E: NTS	U.O.M.: INCHES [mm]		SHEET: 1 (OF 1