

TECHNICAL DATA SHEET

RoHS
Compliant

FLEXIBLE WIRING CABLE

MODELS: PELB0617-PELB0616

APPLICATION

Flexible leads used mainly as a connection to or from test equipment.



ELECTRICAL CHARACTERISTICS

Max. Voltage: 300/500V
Rated Temperature: 70°C
Conductor DC Resistance (Max. @ 20°C): 46.06Ω/km

CONSTRUCTION

Conductor	Plain, annealed copper to EN60228 Class 6
Jacket	PVC

DIMENSIONS

Conductors	Overall Dia.	Length	Colour	Model
55/0.10mm	2.80mm	25m	Black	PELB0617
		100m		PELB0606
		25m	Blue	PELB0607
		100m		PELB0608
		25m	Red	PELB0609
		100m		PELB0610
		25m	Green	PELB0611
		100m		PELB0612
		25m	Yellow	PELB0613
		100m		PELB0614
		25m	White	PELB0615
		100m		PELB0616

Important Notice: This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.