

## Drill chuck with taper chuck

With tapered mount

**ORION**<sup>®</sup>

### Application:

For holding tools with straight shank.

### Execution:

- Body head with keyholes.
- Hardened jaws.
- Keyed drill chuck, DIN ISO 10887.

### Advantage:

- Excellent value for money.
- High clamping force thanks to toothed ring.

### Delivery:

1x 0.8-10 mm/B 12 drill chuck.



<b>Art. no.</b>	<b>21293 010</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	21293010
<b>Min./max. clamping width</b>	0.8-10 mm
<b>Suitable for taper</b>	B 12
<b>Outer diameter</b>	33.5 mm
<b>Gross Weight</b>	0.222 kg
<b>Product Group</b>	207

### EAN

4039247543625