

AC-DC POWER SUPPLIES

15W CONVECTION COOLED

The LCW series of regulated output convection cooled AC-DC power supplies are designed to provide a cost effective solution for industrial electronics and technology applications. Features include wide range AC input from 85-305VAC, output voltage adjustment, low stand-by power consumption, output short circuit protection, over current and over voltage protection. Applications include auxiliary power sources, security installations, lighting control, smart home or office control systems, ticketing and vending applications.

Features

- 15W convection cooled
- Integrated connector cover
- ITE & industrial approvals
- Class B conducted & radiated emissions
- Input voltage range 85-305VAC
- Regulated single outputs from 3.3V to 48VDC
- Output voltage trim ±10%
- Efficiency to 83%
- Short circuit, overvoltage & overload protection
- Conformal coating option
- -30°C to +70°C operating temperature
- 3 year warranty





Dimensions

2.56" x 2.17" x 0.98" (65.0 x 55.0 x 25.0mm)

3.07" x 2.17" x 0.98" (78.0 x 55.0 x 25.0mm) including connector

Models & Ratings

Model Number ⁽³⁾	Out	put Voltage	Output Current	Ripple & Noise	Efficiency ⁽²⁾	Maximum	Power
Model Nulliber.	Nominal	Adjustment Range ⁽⁴⁾	Output Current	pk to pk ⁽¹⁾	Enclency	Capacitive Load	
LCW15US03	3.3V	2.9 - 3.6V	3.0A	80mV	73%	3000µF	10W
LCW15US05	5.0V	4.5 - 5.5V	3.0A	80mV	78%	2400µF	15W
LCW15US12	12.0V	10.8 - 13.8V	1.3A	120mV	82%	1800µF	15W
LCW15US15	15.0V	13.5 - 16.5V	1.0A	120mV	82%	1200µF	15W
LCW15US24	24.0V	21.6 - 26.4V	0.625A	150mV	83%	600µF	15W
LCW15US48	48.0V	43.2 - 52.8V	0.32A	150mV	83%	300µF	15W

Notes:

1. Ripple & noise measured with 20MHz bandwidth and 47µF electrolytic capacitor in parallel with 0.1µF ceramic capacitor.

2. Typical efficiencies measured at 230VAC full load.

3. Add suffix -E to model number to specify conformal coating option, MOQ applies, please contact sales.

4. Output power rating must not be exceeded.

POWERING THE WORLD'S CRITICAL SYSTEMS

Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
	85	115/230	305	VAC	Derate output power linearly from 100% at 100VAC to 80% at 85VAC and from 100% at 277VAC to 80% at 305VAC
Input Voltage - Operating	100		430	VDC	Alternative input. Not to be used in addition to AC input. DC input not included in safety approvals, external DC rated fuse required. Derate output power linearly from 100% at 120VDC to 80% at 100VDC and from 100% at 390VDC to 80% at 430VDC
Input Frequency	47	50/60	63	Hz	
January Comments Full Land			0.35	A	115VAC
Input Current - Full Load			0.25		230VAC
No Load Input Power		0.3		W	
Jamush Quinnant		30		•	115VAC cold start at 25°C ambient
Inrush Current		50		A	230VAC cold start at 25°C ambient
Earth Leakage Current			0.5	mA	277VAC/50Hz
Input Protection	T1.0A/300VAC Internal fuse fitted in line				

Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & C	onditio	ns
Output Voltage	2.9		52.8	VDC	See Mode	ls & Ra	tings table
		±3		%		LCW15US03	
Initial Set Accuracy		±2			Full load	LCW	/15US05
		±1				All o	ther models
Voltage Adjustment		±10		%			
Minimum Load	0			А	No minimu	um load	l required
Start Up Delay		125		ms	115/230VA	C full lo	bad
Held Up Time		7			115VAC		
Hold Up Time		48		ms	230VAC		
Drift			±0.03	%	After 20 m	inutes	warm up, 230VAC, 0°C to 50°C
Line Regulation			±1.0	%	LCW15US	03/05,	100-264VAC, full load
			±0.5	70	All other m	nodels,	100-264VAC, full load
Lood Degulation			±1.0	%	0-100%	0-100% LCW15US03/0	/15US03/05
Load Regulation			±0.5	%	load	All o	ther models
Transient Response			10	%	Recovery within 1% in less than 5ms for a 50-75% and 75-50 step		% in less than 5ms for a 50-75% and 75-50% loa
Ripple & Noise				mV pk-pk	See Models & Ratings table		tings table
Over/Undershoot			10	%	Full load 5	ms reco	overy
			6.75		LCW15US	03/05	
			16.2		LCW15US	12	
Overvoltage Protection			21.8	VDC	LCW15US	15	Hiccup mode, auto recovery
			33.6		LCW15US	24	
			60.0		LCW15US	48	
Overload Protection	110		200	%	Nominal o	utput c	urrent, auto recovery
Temperature Coefficient		±0.03	5	%/°C			
Short Circuit Protection	Continuous	, hiccup with	auto recovery				



AC-DC POWER SUPPLIES

LCW15 Series

General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions		
Efficiency		82		%	230VAC Full load (see Models & Ratings table)		
Isolation: Input to Output	4000			VAC			
Input to Ground	2000			VAC	Class I construction		
Output to Ground	500			VAC			
Switching Frequency		65		kHz			
Power Density			2.75	W/in ³			
Mean Time Between Failure	700			khrs	MIL-HDBK-217F, Notice 2 25°C GB		
Weight		0.198 (90.0)		lb(g)			
Case Material	Aluminium	Aluminium chassis with vented galvanized steel cover					
Conformal Coating Option	Acrvlic res	Acrylic resin, UL94V-0 rated, certified (UL No. E351072), minimum 30µm coating thickness. Add suffix -E to part number					

Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Operating Temperature	-30		+70	°C	See derating curve	
Storage Temperature	-40		+85	°C		
Cooling	Natural convection					
Humidity	5		90	%RH	Non-condensing	
Operating Altitude 5000 m						
Shock and Vibration	Tested according to EN60068-2-27, 10 - 500Hz, 5g (1H) for each X, Y and Z plane					

EMC: Emissions

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55032	Class B	
Radiated	EN55032	Class B	

EMC: Immunity

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
ESD Immunity	EN61000-4-2	3	А	Contact ±6kV/Air ±8kV
Radiated Immunity	EN61000-4-3	3	В	10V/m
EFT	EN61000-4-4	3	А	±2kV
Surge	EN61000-4-5	Installation class 3	А	Line to line ±1kV, line to ground ±2kV
Conducted	EN61000-4-6	3	А	10Vrms
	EN61000-4-11	Dip. 100% (0VAC), 10ms	В	
		Dip. 100% (0VAC), 20ms	В	
Dips		Dip. 60% (88VAC), 200ms	А	
		Dip. 30% (154VAC), 500ms	А	
		Dip. 20% (176VAC), 5000ms	А	
Interruptions		Int. 100% (0VAC), 5000ms	В	




Safety Approvals

Certification	Standard	Notes & Conditions				
UL	UL62368-1	Information Technology				
EN	EN62368-1	Information Technology				
CE	Meets all applicable directives	Meets all applicable directives				
UKCA	Meets all applicable legislation	Meets all applicable legislation				


Application Notes

Temperature Derating





Mechanical Details



Notes:

- 1. All dimensions are in inches (mm).
- 2. Tightening torque: M3, 0.4Nm fixings
- 3. General tolerances: ±0.039 (±1.00)
- 4. Chassis must be connected to protective earth.
- 5. Use 22-14 AWG wire range for connector