

Hydro-expansion chuck type A

Short slimline design

ATORN®

Application

For clamping drill bits and milling tools with straight shank.

Version

- High clamping forces
- With axial length adjustment (max. V in the drawing)
- Highly precise centric clamping
- Outstanding absorption
- Standard tool changes as with expansion chucks without requiring additional devices
- Various applications when used with reducer bushings
- With Balluff chip hole
- Can be clamped with all common shank types

Advantage

- High degree of torque transmission
- Good surface qualities
- Suitable for high rotation speeds
- Excellent vibration-absorbing properties
- Longer service life of cutting tools

Delivery

Tool holder with matching hex key



Art. no.	23733 058
Tool holding device	HSK 63
Overall length	Short-slim
Clamping diameter	25 mm
Form	A
Projecting length	120 mm
Tapered diameter	57 mm
Outer diameter	53 mm
Clearance length to collar	63 mm
Clamp in depth	57 mm
Suitable for thread	M16 x 1
Width across flats	5 mm
Max. adjustment travel	10 mm
Coolant supply	Internal
Balancing quality	G 2.5 at 25 rpm

EAN-Code

4050293 151398