


RANA Linear Surface&Suspended - MicroPrismatic Optic

RANA LINEAR S 3KLM NW MPO EM
0051258



Product features

- Surface or Suspended LED Linear luminaire with Micro Prismatic Optic, Dimensions: 1150mm x 87mm x 87mm, Direct, White Body, Emergency 3 hours maintained, Neutral White LED (4000K), 2890lm, 35W, 83lm/W efficacy, CRI>80, 3 SDCM (3-step MacAdam ellipse), Low LED Flicker (+/-5%), UGR<21, L90B10 at 50,000 hours, Electric Class I, Glow Wire Test 850°C



PRODUCT OVERVIEW

Product name	RANA LINEAR S 3KLM NW MPO EM
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting, Suspended
Fixture rating	Enclosed
Environment	Internal
General application	Office, Hospitality, Retail, Education
ETIM Class	EC002892
Warranty	5 years
Fixture luminous flux (lm)	2890
Luminaire efficacy (lm/W)	82.57
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Colour Consistency (SDCM)	3
Glare control	< 21
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	447
Total power consumption (W)	35
Electrical protection	Class I
Control gear type	Electronic ballast
Dimmable	No
Dimming method	N/A
LED Flickering Rate	Ultra low (5% or less)
Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK07
Product EAN number	5410288512587

RANA Linear Surface&Suspended - MicroPrismatic Optic

RANA LINEAR S 3KLM NW MPO EM
0051258

DATA TABLE

General data

Product name	RANA LINEAR S 3KLM NW MPO EM
Technology	LED
Cap/Base	N/A
Housing	Steel
Mount	Ceiling surface mounting, Suspended
Fixture rating	Enclosed
Environment	Internal
General application	Office, Hospitality, Retail, Education
Operating temperature range (°C)	5°C...+30°C
Performance ambient temperature Tq (°C)	25
ETIM Class	EC002892
Warranty	5 years

Optical data

Fixture luminous flux (lm)	2890
Luminaire efficacy (lm/W)	82.57
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM3
Colour Consistency (SDCM)	3
Adjustable chromaticity	N
Distribution type	Symmetric
Glare control	< 21
Photobiological Risk Group	RG0
Luminous flux (emergency) (lm)	447
Emergency duration (h)	3.0

Electrical data

Total power consumption (W)	35
Mains voltage (V)	220-240V
Lamp power factor	0.95
THD (at 230 V, 50 Hz, full load, at 100% dimming level) xx.x %	20
Electrical protection	Class I
Control gear type	Electronic ballast
Transformer required	Yes
Dimmable	No
Dimming method	N/A
Drive current (mA)	300
Inrush Current (A)	22
Inrush Duration (µs)	250
Glow Wire Test (°C)	850

RANA Linear Surface&Suspended - MicroPrismatic Optic

RANA LINEAR S 3KLM NW MPO EM
0051258

Energy Efficiency Class (A->G) of contained light source	C
Nominal Frequency (Hz)	50/60Hz
LED Flickering Rate	Ultra low (5% or less)
Max. Luminaires per 10A C Breaker	40
Max. Luminaires per 13A C Breaker	51
Max. Luminaires per 16A C Breaker	63
Max. Luminaires per 20A C Breaker	80
Max. Luminaires per 10A B Breaker	15
Max. Luminaires per 13A B Breaker	31
Max. Luminaires per 16A B Breaker	25
Max. Luminaires per 20A B Breaker	48

Lifetime data

Lifespan L70 B50	60000
Lifespan L70 B20	60000
Lifespan L70 B10	60000
Lifespan L80 B50	60000
Lifespan L80 B20	60000
Lifespan L80 B10	60000
Lifespan L90 B50	60000
Lifespan L90 B20	60000
Lifespan L90 B10	60000

Physical data

Housing colour	RAL 9016 - Traffic white / Bezel
IP rating	IP20
IK rating	IK07
Diffuser finish	Prismatic
Diffuser material	PC Polycarbonate
Nominal Product Length (mm)	1150
Nominal Product Width (mm)	87
Nominal Product Height (mm)	87
Weight (kg)	3.45

Packaging





Single packaging type	Carton
Product EAN number	5410288512587
Packaging single length / height (cm)	116.5
Packaging single width (cm)	10.5
Packaging single depth (cm)	10.0
DUN14 (outer)	05410288512587
Units per outer package	1
Packaging outer length / height (cm)	116.5
Packaging outer width (cm)	10.5
Packaging outer depth (cm)	10.0

Safety data

Optimal operating condition (°C)	5-30
----------------------------------	------

RANA Linear Surface & Suspended - MicroPrismatic Optic *RANA LINEAR S 3KLM NW MPO EM* 0051258

PHOTOMETRY



TECHNICAL DRAWINGS

