

LED linear light, flat design

basic set

Application:

The discrete, slender and high-quality construction of the light is impressive in industrial applications owing to the excellent light quality and facilitates custom workstation lighting. With intuitive assembly via adhesive magnets or screws, it is also suitable for discreet mounting on cabinet housings, in draws or on shelving.

Execution:


- high-performance LED in aluminium housing, anodised, visual effect of a transparent panel without colour fringing
- ultra-flat, elegant design
- with touch dimmer module, with on/off and infinitely variable dimming

Advantage:

- low energy consumption thanks to LED technology
- excellent light quality with maximum colour rendering
- maximum service life owing to optimal thermal management
- variable mounting options via retaining clamps with adhesive magnets or screws for individual attachment of lights
- simple extension up to an overall length of max. 3 m is possible by positioning multiple lights in a row using intermediary connectors

Delivery:

incl. 36 W power supply unit, touch dimmer module, retaining clamps for screw or magnet attachment



Art. no.	50239 172
Design	Flat
Width	33 mm
Length	500 mm
Colour	Pearl dark grey RAL 9023
Gross Weight	0.550 kg
Product Group	586