

## Polarising microscopes KERN OPO-1





Bertrand lens, λ Slip, 360° rotatable analyser (removable)



Center-adjustable and turnable polarisation stage



"Swing-Out" condenser

## **PROFESSIONAL LINE POL**

The flexible and powerful polarising microscope for all professional applications with reflected and transmitted light

#### **Features**

- This device is a professional, fully-equipped polarising microscope, which uses the polarisation of light to analyse minerals, crystals and isotropic materials
- The KERN OKO 185 is a combi variant of LED incident illumination and LED transmitted illumination. A height-adjustable 0.9/0.13 Swing-out Abbe condenser which can be centred for complete Köhler illumination are part of the standard version.
- A 360° revolving stage with 1° division, 6' fine division and locking function is integrated into all series as standard
- As standard all series are fitted with a complete polarising unit with scale, a Bertrand lens, a λ + ½ λ Slip as well as a quartz wedge
- A large selection of accessories such as, for example, a mechanical stage attachment as well as further objectives for a long working distance and filter units are also available
- A protective dust cover, eye cups, as well as multi-lingual user instructions are included in the scope of delivery
- A C-Mount adapter is required to connect a camera. You can select this adapter from the following model outfit list
- Please find detailed information in the following model outfit list

#### Scope of application

 Mineralogy, texture observations, material testing, observation of crystals

#### Applications/Samples

More complex samples with polarising properties

## Technical data

- · Infinity optical system
- · Quintuple nosepiece
- Siedentopf 30° inclined
- Diopter adjustment: Both-sided
- Overall dimensions W×D×H 500×200×500 mm
- Net weight approx. 14,5 kg

# STANDARD SOC A D SOC

Model

ilioue:			Otandara	oomigaration	
KERN	Tube	Eyepiece	Objective quality	Objectives	Illumination
OPO 185	Trinocular	HWF 10×/Ø 20 mm	Infinity Plan	Non-stress 4×/10×/20×/40×/50×	5W LED (incident + transmitted)

Standard configuration

# **MICROSCOPES & REFRACTOMETERS 2023**

MICROSCOPES



Polarising microscopes KERN OPO-1

Model outfit		Model KERN	Order number	
		OPO 185		
Eyepieces	HWF 10×/20 mm	✓	OBB-A1591	
(23,2 mm)	HWF 10×/20 mm (reticule 0,1 mm) (adjustable)	✓	OBB-A1592	
Non-stress Infinity	4×/0,10 W.D. 12,1 mm	✓	OBB-A1294	
	10×/0,25 W.D. 4,64 mm	✓	OBB-A1289	
Plan objectives (transmitted)	20×/0,40 (spring-loaded) W.D. 2,41 mm	✓	OBB-A1290	
(transmitted)	40×/0,66 (spring-loaded) W.D. 0,65 mm	✓	OBB-A1292	
	5×/0,13 W.D. 16,04 mm	0	OBB-A1593	
Non-stress	10×/0,25 W.D. 18,48 mm	0	OBB-A1594	
Infinity Plan objectives	20×/0,40 W.D. 8,35 mm	0	OBB-A1291	
(incident) for long working distance	Semi apochromatic 50×/0,75 W.D. 4,25 mm	✓	OBB-A1642	
0	100×/0,85 (dry) (spring-loaded) W.D. 3,00 mm	0	OBB-A1595	
Trinocular tube	<ul> <li>Siedentopf 30° inclined</li> <li>Interpupillary distance 48 – 76 mm</li> <li>Light distribution 100:0</li> </ul>	✓		
Analyser unit with scale	360° rotatable, lockable	✓		
Bertrand lens	Insertable, center-adjustable	✓	OBB-A1121	
λ + ¼ λ Slip	λ Slip and ¼ λ Slip (combination)	✓	OBB-A1316	
Quartz wedge	I - IV Class	✓	OBB-A1321	
Revolving round stage	360° rotatable, center-adjustable, division 1°, Vernier division 6'	✓		
Polarising attached mechanical stage	Polarising attached mechanical stage	0	OBB-A1337	
Swing-out condenser	N.A. 0,9/0,13 swing-out achromatic condenser (aperture diaphragm)	<b>✓</b>	OBB-A1107	
Polarising unit with scale (transmitted)	360° rotatable, lockable	<b>√</b>		
Koehler illumination	5 W LED spare bulb (transmitted)			
Illumination polarising unit	5 W LED spare bulb (incident)	<b>-</b> ✓	OBB-A1589	
	Blue	✓	OBB-A1170	
Colour filters	Green	0	OBB-A1188	
for transmitted illumination	Yellow	0	OBB-A1165	
	Grey	0	OBB-A1183	
	1×	0	OBB-A1514	
C-Mount	0,75×	0	OBB-A1590	
	0,5× (focus adjustable)	0	OBB-A1515	

# **MICROSCOPES & REFRACTOMETERS 2023**

KERN PICTOGRAMS





360° rotatable microscope head



Monocular Microscope For the inspection with one eye



**Binocular Microscope** For the inspection with both eyes



Trinocular Microscope

For the inspection with both eyes and the additional option for the connection of a camera



Abbe Condenser

With high numerical aperture for the concentration and the focusing of light



Halogen illumination

For pictures bright and rich in contrast



**LED** illumination

Cold, energy-saving and especially long-life illumination



Incident illumination

For non-transparent objects



Transmitting illumination

For transparent objects



Fluorescence illumination

For stereomicroscopes



Fluorescence illumination for compound microscopes

With 100 W mercury lamp and filter



Fluorescence illumination **for compound microscopes**With 3 W LED illumination and filter



Phase contrast unit

For a higher contrast



Darkfield condenser/unit

For a higher contrast due to indirect illumination



Polarising unit

To polarise the light

00

Infinity system

Infinity corrected optical system



Zoom magnification

For stereomicroscopes



Auto-focus

For automatic control of the focus level



Parallel optical system

For stereomicroscopes, enables fatigue-proof working



Integrated scale

In the eyepiece



SD card

For data storage



USB 2.0 digital camera

For direct transmitting of the picture to a PC



USB 3.0 digital camera

For direct transmitting of the picture to a PC



WIFI data interface:

For transmitting of the picture to a mobile display device



**HDMI** digital camera

For direct transmitting of the picture to a display device



PC software

To transfer the measurements from the device to a PC.



Automatic temperature compesation

For measurements between 10 °C and 30 °C



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013

**ABBREVIATIONS** 

C-Mount Adapter for the connection of a camera to a trinocular microscope

**FPS** Frames per second

High (Super) Wide Field (Eyepiece with high eye point for wearers of glasses) H(S)WF

LWD Long Working Distance N.A. **Numerical Aperture** SLR camera Single-Lens Reflex camera

**SWF** Super Wide Field (Field number at least Ø 23 mm for 10× eyepiece)

W.D. Working Distance

WF Wide Field (Field number up to Ø 22 mm for 10× eyepiece)

BATT

**Battery operation** 

Ready for battery operation. The battery type is specified for each device.



Battery operation rechargeable Prepared for a rechargeable battery

operation

**Plug-in power supply** 230V/50Hz in standard version for EU. On request GB, AUS or USA version.



Integrated power supply unit

Integrated in microscope. 230V/50Hz standard EU. More standards e.g. GB, AUS or USA on request.



Package shipment

The time required to manufacture the product internally is shown in days in the pictogram.