



## SAFETY DATA SHEET TRIPLE R 5W30 FORD FULLY SYNTHETIC

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

**Product name** TRIPLE R 5W30 FORD FULLY SYNTHETIC

**Product number** XLJ010, XLJ050, XRJ001, XRJ004

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Identified uses** Engine oil.

#### 1.3. Details of the supplier of the safety data sheet

**Supplier** TETROSYL LIMITED  
Bury  
Lancashire  
England  
BL9 7NY  
0161 764 5981  
0161 797 5899  
info@tetrosyl.com

**Manufacturer** TETROSYL LIMITED  
Bury  
Lancashire  
England  
BL9 7NY  
0161 764 5981  
0161 797 5899  
info@tetrosyl.com

#### 1.4. Emergency telephone number

**Emergency telephone** +44 (0)161 764 5981

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (EC 1272/2008)

**Physical hazards** Not Classified

**Health hazards** Not Classified

**Environmental hazards** Aquatic Chronic 3 - H412

#### 2.2. Label elements

**Hazard statements** H412 Harmful to aquatic life with long lasting effects.

**Precautionary statements** P273 Avoid release to the environment.  
P501 Dispose of contents/ container in accordance with national regulations.  
P101 If medical advice is needed, have product container or label at hand.  
P102 Keep out of reach of children.

## TRIPLE R 5W30 FORD FULLY SYNTHETIC

### 2.3. Other hazards

Not applicable.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

<p><b>LUBRICATING OILS, (PETROLEUM), C20-50, HYDROTREATED NEUTRAL OIL-BASED &lt;3% DMSO EXTRACT (IP346)</b></p> <p>CAS number: 72623-87-1                      EC number: 276-738-4                      REACH registration number: 01- 2119474889-13</p>	<p><b>30-&lt;60%</b></p>
<p><b>Classification</b> Asp. Tox. 1 - H304</p>	
<p><b>DISTILLATES, HYDROTREATED HEAVY PARAFFINIC &lt;3% DMSO EXTRACT (IP 346)</b></p> <p>CAS number: 64742-54-7                      EC number: 265-157-1                      REACH registration number: 01- 2119484627-25-0000</p>	<p><b>10-&lt;30%</b></p>
<p><b>Classification</b> Asp. Tox. 1 - H304</p>	
<p><b>MINERAL OIL - H304 (&lt;3% DMSO EXTRACT, IP 346)</b></p> <p>CAS number: 64742-55-8                      EC number: 265-158-7                      REACH registration number: 01- 2119487077-29-0000</p>	<p><b>5-&lt;10%</b></p>
<p><b>Classification</b> Asp. Tox. 1 - H304</p>	
<p><b>PHOSPHORODITHIOIC ACID, MIXED O,O-BIS (1,3- DIMETHYLBUTYL AND ISO-PR)ESTERS, ZINC SALTS</b></p> <p>CAS number: 84605-29-8                      EC number: 283-392-8                      REACH registration number: 01- 2119493626-26-0000</p>	<p><b>1-&lt;2%</b></p>
<p><b>Classification</b> Skin Irrit. 2 - H315 Eye Dam. 1 - H318 Aquatic Chronic 2 - H411</p>	

## TRIPLE R 5W30 FORD FULLY SYNTHETIC

<b>PHENOL, DODECYL-, BRANCHED</b> <span style="float: right;">-&lt;0.05</span>		
CAS number: 121158-58-5	EC number: 310-154-3	REACH registration number: 01-2119513207-49-0000
M factor (Acute) = 10	M factor (Chronic) = 10	
<b>Classification</b>		
Skin Corr. 1C - H314		
Eye Dam. 1 - H318		
Repr. 1B - H360F		
Aquatic Acute 1 - H400		
Aquatic Chronic 1 - H410		
<b>BUTYLATED HYDROXYTOLUENE</b> <span style="float: right;">-&lt;0.05</span>		
CAS number: 128-37-0	EC number: 204-881-4	REACH registration number: 01-2119565113-46-0000
M factor (Acute) = 1	M factor (Chronic) = 1	
<b>Classification</b>		
Aquatic Acute 1 - H400		
Aquatic Chronic 1 - H410		
<b>DIPHENYLAMINE</b> <span style="float: right;">-&lt;0.05</span>		
CAS number: 122-39-4	EC number: 204-539-4	
M factor (Acute) = 1	M factor (Chronic) = 1	
<b>Classification</b>		
Acute Tox. 3 - H301		
Acute Tox. 3 - H311		
Acute Tox. 3 - H331		
STOT RE 2 - H373		
Aquatic Acute 1 - H400		
Aquatic Chronic 1 - H410		

The full text for all hazard statements is displayed in Section 16.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

<b>General information</b>	Get medical attention if any discomfort continues. Remove affected person from source of contamination. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing.
<b>Inhalation</b>	If spray/mist has been inhaled, proceed as follows. Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing.
<b>Ingestion</b>	Contact physician if larger quantity has been consumed. Rinse mouth thoroughly with water.
<b>Skin contact</b>	Remove contaminated clothing immediately and wash skin with soap and water. Get medical attention if irritation persists after washing.
<b>Eye contact</b>	Rinse immediately with plenty of water. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Do not rub eye.

## TRIPLE R 5W30 FORD FULLY SYNTHETIC

### 4.2. Most important symptoms and effects, both acute and delayed

<b>General information</b>	The severity of the symptoms described will vary dependent on the concentration and the length of exposure. Effects may be delayed. Keep affected person under observation.
<b>Inhalation</b>	May cause an asthma-like shortness of breath. Vapours may cause headache, fatigue, dizziness and nausea.
<b>Ingestion</b>	May cause discomfort if swallowed. May cause stomach pain or vomiting. May cause nausea, headache, dizziness and intoxication.
<b>Skin contact</b>	Prolonged or repeated contact with skin may cause irritation, redness and dermatitis. Allergic rash.
<b>Eye contact</b>	May cause temporary eye irritation.

### 4.3. Indication of any immediate medical attention and special treatment needed

<b>Notes for the doctor</b>	No specific recommendations. If in doubt, get medical attention promptly.
-----------------------------	---

## SECTION 5: Firefighting measures

### 5.1. Extinguishing media

<b>Suitable extinguishing media</b>	Extinguish with the following media: Foam, carbon dioxide or dry powder. Use fire-extinguishing media suitable for the surrounding fire.
<b>Unsuitable extinguishing media</b>	Do not use water jet as an extinguisher, as this will spread the fire.

### 5.2. Special hazards arising from the substance or mixture

<b>Specific hazards</b>	Fire creates: Carbon monoxide (CO). Carbon dioxide (CO <sub>2</sub> ). No unusual fire or explosion hazards noted.
<b>Hazardous combustion products</b>	Thermal decomposition or combustion may liberate carbon oxides and other toxic gases or vapours. Oxides of carbon.

### 5.3. Advice for firefighters

<b>Special protective equipment for firefighters</b>	Leave danger zone immediately.
--	--------------------------------

## SECTION 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

<b>Personal precautions</b>	Follow precautions for safe handling described in this safety data sheet. Avoid inhalation of vapours. Avoid contact with eyes and prolonged skin contact. Provide adequate ventilation. In case of spills, beware of slippery floors and surfaces.
-----------------------------	---

### 6.2. Environmental precautions

<b>Environmental precautions</b>	Avoid discharge into drains or watercourses or onto the ground. Collect and dispose of spillage as indicated in Section 13.
----------------------------------	---

### 6.3. Methods and material for containment and cleaning up

<b>Methods for cleaning up</b>	Stop leak if possible without risk. Eliminate all sources of ignition. No smoking, sparks, flames or other sources of ignition near spillage. Provide adequate ventilation. Provide adequate ventilation. Contain spillage with sand, earth or other suitable non-combustible material. Avoid the spillage or runoff entering drains, sewers or watercourses. Absorb spillage with non-combustible, absorbent material. Collect and place in suitable waste disposal containers and seal securely.
--------------------------------	--

### 6.4. Reference to other sections

## TRIPLE R 5W30 FORD FULLY SYNTHETIC

**Reference to other sections** Wear protective clothing as described in Section 8 of this safety data sheet. Collect and dispose of spillage as indicated in Section 13.

### SECTION 7: Handling and storage

#### 7.1. Precautions for safe handling

**Usage precautions** Good personal hygiene procedures should be implemented. Wash hands and any other contaminated areas of the body with soap and water before leaving the work site. Do not eat, drink or smoke when using the product. Avoid the formation of mists. Provide adequate ventilation. Avoid contact with skin and eyes. Always remove oil with soap and water or skin cleaning agent, never use organic solvents. Do not use oil-contaminated clothing or shoes, and do not put rags moistened with oil into pockets.

#### 7.2. Conditions for safe storage, including any incompatibilities

**Storage precautions** Keep containers upright. Store in tightly-closed, original container.

#### 7.3. Specific end use(s)

**Specific end use(s)** The identified uses for this product are detailed in Section 1.2.

### SECTION 8: Exposure controls/Personal protection

#### 8.1. Control parameters

##### Occupational exposure limits

No exposure limits known for ingredient(s).

##### BUTYLATED HYDROXYTOLUENE

Long-term exposure limit (8-hour TWA): WEL 10 mg/m<sup>3</sup>

##### DIPHENYLAMINE

Long-term exposure limit (8-hour TWA): WEL 10 mg/m<sup>3</sup>

Short-term exposure limit (15-minute): WEL 20 mg/m<sup>3</sup>

WEL = Workplace Exposure Limit.

#### 8.2. Exposure controls

##### Protective equipment



##### Appropriate engineering controls

Provide adequate ventilation. Avoid inhalation of vapours. Observe any occupational exposure limits for the product or ingredients.

##### Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. Unless the assessment indicates a higher degree of protection is required, the following protection should be worn: Tight-fitting safety glasses.

##### Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. It is recommended that gloves are made of the following material: Nitrile rubber. It should be noted that liquid may penetrate the gloves. Frequent changes are recommended.

##### Other skin and body protection

Wear suitable protective clothing as protection against splashing or contamination.

##### Hygiene measures

Wash contaminated clothing before reuse. Wash promptly with soap and water if skin becomes contaminated.

##### Respiratory protection

No specific recommendations.

## TRIPLE R 5W30 FORD FULLY SYNTHETIC

### SECTION 9: Physical and chemical properties

#### 9.1. Information on basic physical and chemical properties

<b>Appearance</b>	Clear liquid.
<b>Colour</b>	Brown.
<b>Odour</b>	Oil-like.
<b>pH</b>	Not determined.
<b>Melting point</b>	Not determined.
<b>Initial boiling point and range</b>	>250°C @ 1013 hPa
<b>Flash point</b>	208°C
<b>Evaporation rate</b>	Not determined.
<b>Upper/lower flammability or explosive limits</b>	Not determined.
<b>Vapour pressure</b>	Not determined.
<b>Vapour density</b>	Not determined.
<b>Relative density</b>	0.854g/cm <sup>3</sup> @ 20°C
<b>Solubility(ies)</b>	Insoluble in water.
<b>Partition coefficient</b>	Not determined.
<b>Auto-ignition temperature</b>	Not determined.
<b>Decomposition Temperature</b>	Not determined.
<b>Viscosity</b>	53 mm <sup>2</sup> /s @ 40°C

#### 9.2. Other information

<b>Other information</b>	None.
--------------------------	-------

### SECTION 10: Stability and reactivity

#### 10.1. Reactivity

<b>Reactivity</b>	There are no known reactivity hazards associated with this product.
-------------------	---

#### 10.2. Chemical stability

<b>Stability</b>	No particular stability concerns.
------------------	-----------------------------------

#### 10.3. Possibility of hazardous reactions

<b>Possibility of hazardous reactions</b>	Not applicable.
---	-----------------

#### 10.4. Conditions to avoid

<b>Conditions to avoid</b>	There are no known conditions that are likely to result in a hazardous situation.
----------------------------	---

#### 10.5. Incompatible materials

<b>Materials to avoid</b>	No specific material or group of materials is likely to react with the product to produce a hazardous situation.
---------------------------	--

#### 10.6. Hazardous decomposition products

## TRIPLE R 5W30 FORD FULLY SYNTHETIC

**Hazardous decomposition products** Does not decompose when used and stored as recommended.

### SECTION 11: Toxicological information

#### 11.1. Information on toxicological effects

**Toxicological effects** No information available.

### SECTION 12: Ecological information

**Ecotoxicity** Harmful to aquatic life with long lasting effects.

#### 12.1. Toxicity

##### Acute aquatic toxicity

**Acute toxicity - fish** Not available.

**Acute toxicity - aquatic invertebrates** Not available.

#### 12.2. Persistence and degradability

**Persistence and degradability** There are no data on the degradability of this product.

#### 12.3. Bioaccumulative potential

**Bioaccumulative potential** No data available on bioaccumulation.

**Partition coefficient** Not determined.

#### 12.4. Mobility in soil

**Adsorption/desorption coefficient** Not available.

#### 12.5. Results of PBT and vPvB assessment

**Results of PBT and vPvB assessment** This substance is not classified as PBT or vPvB according to current EU criteria.

#### 12.6. Other adverse effects

**Other adverse effects** Not available.

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

**General information** Waste is classified as hazardous waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

**Disposal methods** Confirm disposal procedures with environmental engineer and local regulations.

### SECTION 14: Transport information

**General** The product is not covered by international regulations on the transport of dangerous goods (IMDG, IATA, ADR/RID).

#### 14.1. UN number

Not applicable.

#### 14.2. UN proper shipping name

Not applicable.

#### 14.3. Transport hazard class(es)

## TRIPLE R 5W30 FORD FULLY SYNTHETIC

No transport warning sign required.

### 14.4. Packing group

Not applicable.

### 14.5. Environmental hazards

**Environmentally hazardous substance/marine pollutant**

No.

### 14.6. Special precautions for user

Not applicable.

### 14.7. Transport in bulk according to Annex II of MARPOL and the IBC Code

Transport in bulk according to Not applicable.

**Annex II of MARPOL 73/78  
and the IBC Code**

## SECTION 15: Regulatory information

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

**National regulations** EH40/2005 Workplace exposure limits.

**EU legislation** Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).  
Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

### 15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

## SECTION 16: Other information

**Revision comments** NOTE: Lines within the margin indicate significant changes from the previous revision.

**Issued by** Health & Safety Department

**Revision date** 18/03/2020

**Revision** 5

**Supersedes date** 30/01/2020

**SDS status** Approved.



## TRIPLE R 5W30 FORD FULLY SYNTHETIC

### Hazard statements in full

H301 Toxic if swallowed.  
H304 May be fatal if swallowed and enters airways.  
H311 Toxic in contact with skin.  
H314 Causes severe skin burns and eye damage.  
H315 Causes skin irritation.  
H318 Causes serious eye damage.  
H331 Toxic if inhaled.  
H360F May damage fertility.  
H373 May cause damage to organs through prolonged or repeated exposure.  
H400 Very toxic to aquatic life.  
H410 Very toxic to aquatic life with long lasting effects.  
H411 Toxic to aquatic life with long lasting effects.  
H412 Harmful to aquatic life with long lasting effects.