

RELAY 1CH.CONT. HARD GOLD-PLAT. COIL  
VOLTAGE 60 V DC FOR USE IN 110/230 V AC/DC  
CABINET UNIT

General technical data:

Type of voltage		DC
Control supply voltage		
<ul style="list-style-type: none"> <li>• for DC Rated value</li> <li>— minimum</li> <li>— maximum</li> </ul>	V V	60 60
Switching behavior		monostable
Number of NC contacts for auxiliary contacts		0
Number of NO contacts for auxiliary contacts		0
Number of CO contacts for auxiliary contacts		1
Operating current of the auxiliary contacts		
<ul style="list-style-type: none"> <li>• at DC-13</li> <li>— at 24 V</li> <li>— at 110 V</li> <li>— at 230 V</li> <li>• at AC-15</li> <li>— at 230 V</li> </ul>	A A A A	1 0.2 0.1 3
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		K
Equipment marking acc. to DIN EN 61346-2		K

Mechanical data:

Type of electrical connection Plug-in socket		No
Design of the relay operating mechanism		poled
Design of the switching function positively driven		No
Product component Plug-in socket		No

Ambient conditions:

Protection class IP		IP00
Ambient temperature during operation	°C	-25 ... +55

Certificates/ approvals:



[Declaration of Conformity](#)

#### Further information

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/industrial-controls/catalogs>

**Industry Mall (Online ordering system)**

<http://www.siemens.com/industrymall>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3TX70147BP02>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3TX70147BP02>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=3TX70147BP02&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3TX70147BP02&lang=en)

last modified:

15.01.2015