



SIMATIC S7-1500, ANALOG INPUT MODULE AI 8 X U/I/RTD/TC, 16 BITS OF RESOLUTION, ACCURACY 0.3 %; 8 CHANNELS IN GROUPS OF 8; 4 CHANNELS FOR RTD MEASURING, COMMON MODE VOLTAGE APPR. 10 V; DIAGNOSIS, PROCESSALARMS INCL. INFEEED ELEMENT, SHIELD CLAMP AND SHIELD TERMINAL

Product type designation	
General information	
HW functional status	E01
Firmware version	V2.0.0
Product function	
• I&M data	Yes; I&M0 to I&M3
Engineering with	
• STEP 7 TIA Portal can be configured/integrated as of version	V12 / V12
• STEP 7 can be configured/integrated as of version	V5.5 SP3 / -
• PROFIBUS as of GSD version/GSD revision	V1.0 / V5.1
• PROFINET as of GSD version/GSD revision	V2.3 / -
Operating mode	
• MSI	Yes
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	

Current consumption, max.	240 mA; with 24 V DC supply
Encoder supply	
24 V encoder supply	
• short-circuit protection	Yes
• Output current, max.	53 mA
Power	
Power available from the backplane bus	0.7 W
Power losses	
Power loss, typ.	2.7 W
Analog inputs	
Number of analog inputs	8
• For current measurement	8
• For voltage measurement	8
• For resistance/resistance thermometer measurement	4
• For thermocouple measurement	8
permissible input voltage for voltage input (destruction limit), max.	28.8 V
permissible input current for current input (destruction limit), max.	40 mA
Technical unit for temperature measurement adjustable	Yes
Input ranges (rated values), voltages	
• 1 V to 5 V	Yes
• Input resistance (1 V to 5 V)	100 k Ω
• -1 V to +1 V	Yes
• Input resistance (-1 V to +1 V)	10 M Ω
• -10 V to +10 V	Yes
• Input resistance (-10 V to +10 V)	100 k Ω
• -2.5 V to +2.5 V	Yes
• Input resistance (-2.5 V to +2.5 V)	10 M Ω
• -250 mV to +250 mV	Yes
• Input resistance (-250 mV to +250 mV)	10 M Ω
• -5 V to +5 V	Yes
• Input resistance (-5 V to +5 V)	100 k Ω
• -50 mV to +50 mV	Yes
• Input resistance (-50 mV to +50 mV)	10 M Ω
• -500 mV to +500 mV	Yes
• Input resistance (-500 mV to +500 mV)	10 M Ω
• -80 mV to +80 mV	Yes
• Input resistance (-80 mV to +80 mV)	10 M Ω

Input ranges (rated values), currents	
• 0 to 20 mA	Yes
• Input resistance (0 to 20 mA)	25 Ω; Plus approx. 42 ohms for overvoltage protection by PTC
• -20 mA to +20 mA	Yes
• Input resistance (-20 mA to +20 mA)	25 Ω; Plus approx. 42 ohms for overvoltage protection by PTC
• 4 mA to 20 mA	Yes
• Input resistance (4 mA to 20 mA)	25 Ω; Plus approx. 42 ohms for overvoltage protection by PTC
Input ranges (rated values), thermoelements	
• Type B	Yes
• Input resistance (Type B)	10 MΩ
• Type E	Yes
• Input resistance (Type E)	10 MΩ
• Type J	Yes
• Input resistance (type J)	10 MΩ
• Type K	Yes
• Input resistance (Type K)	10 MΩ
• Type N	Yes
• Input resistance (Type N)	10 MΩ
• Type R	Yes
• Input resistance (Type R)	10 MΩ
• Type S	Yes
• Input resistance (Type S)	10 MΩ
• Type T	Yes
• Input resistance (Type T)	10 MΩ
Input ranges (rated values), resistance thermometer	
• Ni 100	Yes; Standard/climate
• Input resistance (Ni 100)	10 MΩ
• Ni 1000	Yes; Standard/climate
• Input resistance (Ni 1000)	10 MΩ
• LG-Ni 1000	Yes; Standard/climate
• Input resistance (LG-Ni 1000)	10 MΩ
• Pt 100	Yes; Standard/climate
• Input resistance (Pt 100)	10 MΩ
• Pt 1000	Yes; Standard/climate
• Input resistance (Pt 1000)	10 MΩ
• Pt 200	Yes; Standard/climate
• Input resistance (Pt 200)	10 MΩ
• Pt 500	Yes; Standard/climate
• Input resistance (Pt 500)	10 MΩ
Input ranges (rated values), resistors	
• 0 to 150 ohms	Yes

• Input resistance (0 to 150 ohms)	10 MΩ
• 0 to 300 ohms	Yes
• Input resistance (0 to 300 ohms)	10 MΩ
• 0 to 600 ohms	Yes
• Input resistance (0 to 600 ohms)	10 MΩ
• 0 to 6000 ohms	Yes
• Input resistance (0 to 6000 ohms)	10 MΩ
• PTC	Yes
• Input resistance (PTC)	10 MΩ
Thermocouple (TC)	
• Technical unit for temperature measurement	°C/°F/K
Temperature compensation	
— Parameterizable	Yes
— internal temperature compensation	Yes
— External temperature compensation via RTD	Yes
— Compensation for 0 °C reference point temperature	Yes; fixed value can be set
Resistance thermometer (RTD)	
• Technical unit for temperature measurement	°C/°F/K
Cable length	
• shielded, max.	800 m; for U/I, 200 m for R/RTD, 50 m for TC
Analog value generation for the inputs	
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Integration time (ms)	2,5 / 16,67 / 20 / 100 ms
• Basic conversion time, including integration time (ms)	9 / 23 / 27 / 107 ms
— additional conversion time for wire break monitoring	9 ms
— additional conversion time for resistance measurement	150 ohm, 300 ohm, 600 ohm, Pt100, Pt200, Ni100: 2 ms 6000 ohm, Pt500, Pt1000, Ni1000, LG-Ni1000, PTC: 4 ms
Smoothing of measured values	
• Parameterizable	Yes
• Step: None	Yes
• Step: low	Yes
• Step: Medium	Yes
• Step: High	Yes
Encoder	
Connection of signal encoders	

- for voltage measurement
- for current measurement as 2-wire transducer
 - Burden of 2-wire transmitter, max.
- for current measurement as 4-wire transducer
- for resistance measurement with two-wire connection
- for resistance measurement with three-wire connection
- for resistance measurement with four-wire connection

Yes
 Yes
 820 Ω
 Yes
 Yes; Only for PTC

 Yes; All measuring ranges except PTC; internal compensation of the cable resistances
 Yes; All measuring ranges except PTC

Errors/accuracies

Linearity error (relative to input range), (+/-)	0.02 %
Temperature error (relative to input range), (+/-)	0.005 %/K; with TC type T 0.02 +/- %/K
Crosstalk between the inputs, max.	-80 dB
Repeat accuracy in steady state at 25 °C (relative to input area), (+/-)	0.02 %
Temperature error of internal compensation	+/-6 °C

Operational limit in overall temperature range

- Voltage, relative to input area, (+/-) 0.3 %
- Current, relative to input area, (+/-) 0.3 %
- Resistance, relative to input area, (+/-) 0.3 %
- Resistance thermometer, relative to input area, (+/-)
Pt xxx standard: ±1.5 K, Pt xxx climate: ±0.5 K, Ni xxx standard: ±0.5 K, Ni xxx climate: ±0.3 K
- Thermocouple, relative to input area, (+/-)
Type B: > 600 °C ±4.6 K, type E: > -200 °C ±1.5 K, type J: > -210 °C ±1.9 K, type K: > -200 °C ±2.4 K, type N: > -200 °C ±2.9 K, type R: > 0 °C ±4.7 K, type S: > 0 °C ±4.6 K, type T: > -200 °C ±2.4 K

Basic error limit (operational limit at 25 °C)

- Voltage, relative to input area, (+/-) 0.1 %
- Current, relative to input area, (+/-) 0.1 %
- Resistance, relative to input area, (+/-) 0.1 %
- Resistance thermometer, relative to input area, (+/-)
Pt xxx standard: ±0.7 K, Pt xxx climate: ±0.2 K, Ni xxx standard: ±0.3 K, Ni xxx climate: ±0.15 K
- Thermocouple, relative to input area, (+/-)
Type B: > 600 °C ±1.7 K, type E: > -200 °C ±0.7 K, type J: > -210 °C ±0.8 K, type K: > -200 °C ±1.2 K, type N: > -200 °C ±1.2 K, type R: > 0 °C ±1.9 K, type S: > 0 °C ±1.9 K, type T: > -200 °C ±0.8 K

Interference voltage suppression for $f = n \times (f_1 \pm 1 \%)$, f_1 = interference frequency

- Series mode interference (peak value of interference < rated value of input range), min. 40 dB
- common mode voltage, max. 10 V
- Common mode interference, min. 60 dB

Interrupts/diagnostics/status information

Alarms	
• Diagnostic alarm	Yes
• Limit value alarm	Yes; two upper and two lower limit values in each case
Diagnostic messages	
• Diagnostics	Yes
• Monitoring the supply voltage	Yes
• Wire break	Yes; Only for 1 to 5 V, 4 to 20 mA, TC, R, and RTD
• Overflow/underflow	Yes
Diagnostics indication LED	
• RUN LED	Yes; Green LED
• ERROR LED	Yes; Red LED
• Monitoring of the supply voltage (PWR-LED)	Yes; Green LED
• Channel status display	Yes; Green LED
• for channel diagnostics	Yes; Red LED
• for module diagnostics	Yes; Red LED
Electrical isolation channels	
• between the channels	No
• between the channels, in groups of	8
• between the channels and the backplane bus	Yes
• between the channels and the supply voltage of the electronics	Yes
Permissible potential difference	
between the inputs (UCM)	20 V DC
between inputs and MANA (UCM)	10 V DC
between M internally and the inputs	75 V DC/60 V AC (base isolation)
Isolation	
Isolation checked with	707 V DC (type test)
Decentralized operation	
Prioritized startup	No
Dimensions	
Width	35 mm
Height	147 mm
Depth	129 mm
Weights	
Weight, approx.	310 g
other	
Note:	Additional basic error and noise for integration time = 2.5 ms: Voltage: ± 250 mV ($\pm 0.02\%$), ± 80 mV ($\pm 0.05\%$), ± 50 mV ($\pm 0.05\%$); resistance: 150 ohms $\pm 0.02\%$; resistance thermometer: Pt100 climate: ± 0.08 K, Ni100 climate: ± 0.08 K; thermocouple: Type B, R, S: ± 3 K, type E, J, K, N, T: ± 1 K

last modified:

12.03.2015