

Product type designation	RUGGEDCOM GBIC FG73
Product description	2 x 1000LX GBIC - Singlemode, 1310 nm, SC, 70 km RUGGEDCOM GBIC 1000LX GBIC SINGLE MODE SC, LONG REACH 70KM, 1550NM
Suitability for operation	RSG2xxx
Interfaces	
Number of electrical/optical connections / for network components or terminal equipment / maximum	2
Number of optical interfaces / for network components or terminal equipment / maximum	2
Number of 1000 Mbit/s SC ports (LX)	2
Range / at the optical interface / depending on the optical fiber used	70 km
Permitted ambient conditions	
Ambient temperature	
• during operation	-40 ... +85 °C
• during storage	-40 ... +85 °C
• during transport	-40 ... +85 °C
• Note	A maximum ambient operating temperature of +85 °C is permissible for a duration of 16 hours
Relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP20
Design, dimensions and weight	
Design	Media module
Coating	no
Mounting type	screwed
• Installation in media module slot	Yes
Standards, specifications, approvals	
Standard	
• for EMC	FCC Part 15 (Class A), EN55022 (CISPR22 Class A)
• for safety / from CSA and UL	UL 60950-1, CSA C22.2 No. 60950-7
• for hazardous zone / from CSA and UL	Hazardous Locations: Class 1 Division 2
• for emitted interference	EN 61000-6-4 (Class A)
• for interference immunity	EN 61000-6-2
Certificate of suitability	EN 61000-6-2, EN 61000-6-10
• CE marking	Yes
• C-Tick	No

- KC approval
- E1 approval
- IEC 61850-3

No
No
Yes

Further Information / Internet Links

Internet-Link

- to website: Industry Mall/RUGGEDCOM selector
- to website: Siemens RUGGEDCOM
- to website: Selector for cables and connectors
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://ruggedcom-selector.automation.siemens.com>

<http://siemens.com/ruggedcom>

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/automation/net/catalog>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

16.03.2015