

# Keysight U1240 Series Handheld Digital Multimeters

Data Sheet



## Key Features

### Check more, fix more

- 10,000-count display
- 0.09% basic DCV accuracy
- True RMS AC measurement
- Basic functions – ACV, DCV, ACI, DCI, resistance, frequency, diode, continuity tests
- Advanced functions – Capacitance, temperature, MINMAX recording

### Ease of use

- Adjustable backlighting – two intensity levels
- Manual data logging (U1242B only)
- Built-in switch counter, harmonic ratio (U1242B only), dual/differential temperature capabilities (U1242B only)

### Built to last

- Overmold body casing
- CAT III 1000 V and CAT IV 600 V safety protection
- Certified to CE and CSA standards
- Operating temperature –10 to 55 °C

Keysight Technologies, Inc. U1240 Series handheld digital multimeters enable you to check more with wider measurement ranges. They feature true RMS readings on their 10,000-count displays. The adjustable backlighting allows you to complete your jobs even in subdued lighting conditions, or to simply prolong battery life. Your maintenance tasks are greatly simplified due to the built-in switch counter, harmonic ratio, dual and differential temperature capabilities, with just a press of the button. The meters have a high safety rating with CAT III 1000 V and CAT IV 600 V protection and are certified to CE and CSA standards. On top of that, the U1240 Series comes with a certificate of calibration and test report – at no extra cost.

The latest multimeters in this series, the U1241B and U1242B, now come in vivid orange cases, offering the capabilities and functions you need.

## Functions and ranges at a glance

MINMAX recording

Resistance: 0.1  $\Omega$  to 100 M $\Omega$

Backlight: Two intensity levels

Diode test switch counter

DCV: 0.1m V to 1000 V  
ACV: 50m V to 1000 V  
Harmonic ratio (U1242B only)

T1-T2 Differential temperature (U1242B only)

Ambient temperature

Capacitance: 0.1 nF to 10 mF

AC $\mu$ A: 50  $\mu$ A to 10 mA

Frequency: 1 Hz to 200 kHz

Manual data logging (U1242B only)

ACmA: 5 mA to 440 mA

ACA: 0.5 A to 10 A

Temperature: -40 to 1000 °C

## Electrical Specifications

### DC specifications

Function	Range	Resolution	Test current/burden voltage	Accuracy $\pm$ (% of reading + counts of least significant digit)	
				U1241B	U1242B
Voltage <sup>1</sup>	1000.0 mV	0.1 mV	-		0.09% + 5
	10.000 V	0.001 V	-		0.09% + 2
	100.00 V	0.01 V	-		
	1000.0 V	0.1 V	-		0.15% + 5
Current	1000.0 $\mu$ A	0.1 $\mu$ A	< 0.06 V (50 $\Omega$ )		0.1% + 3
	10000 $\mu$ A	1 $\mu$ A	< 0.55 V (50 $\Omega$ )		0.1% + 3
	100.00 mA	0.01 mA	< 0.18 V (0.5 $\Omega$ )		0.2% + 3
	440.0 mA <sup>2</sup>	0.1 mA	< 0.8 V (0.5 $\Omega$ )		0.5% + 3
	10.000 A <sup>3</sup>	0.001 A	< 0.4 V (0.01 $\Omega$ )		0.6% + 5
Resistance <sup>4</sup>	1000.0 $\Omega$ <sup>5</sup>	0.1 $\Omega$	0.5 mA		
	10.000 k $\Omega$ <sup>5</sup>	0.001 k $\Omega$	50 $\mu$ A		
	100.00 k $\Omega$	0.01 k $\Omega$	4.91 $\mu$ A		0.3% + 3
	1000.0 k $\Omega$	0.1 k $\Omega$	447 nA		
	10.000 M $\Omega$	0.001 M $\Omega$	112 nA		0.8% + 3
	100.00 M $\Omega$ <sup>6</sup>	0.01 M $\Omega$	112 nA		1.5% + 3
Diode test <sup>7</sup>	1 V	0.001 V	approximately 0.5 mA		0.3% + 2

1. Input impedance: 10 M $\Omega$  (nominal).
2. Current can be measured up to 440 mA continuously. An additional 0.2% needs to be added to the specified accuracy if the signal measured is in the range of 440 mA to 1100 mA for 30 seconds maximum. After measuring a current of > 440 mA, leave the meter to cool down for twice the measuring time used before applying a low current measurement.
3. Current can be measured up to 10 A continuously with a maximum operating temperature of 50 °C. An additional 0.3% needs to be added to the specified accuracy if the signal measured is in the range of 10 A to 19.999 A for 15 seconds maximum. After measuring a current of > 10 A, leave the meter to cool down for 60 seconds before applying a low current measurement.
4. The maximum open voltage is < 2.8 V. For instant continuity, the built-in buzzer sounds when resistance is < 10.0  $\Omega$ .
5. The accuracy of 1 k $\Omega$  and 10 k $\Omega$  is specified after Null function, which is used to substrate the test lead resistance and the thermal effect.
6. For the range of 100 M $\Omega$ , the R.H. is specified for < 60%. The temperature coefficient will be 0.15 times of specified accuracy as > 50 M $\Omega$ .
7. Overload protection: 1000 V RMS for circuits < 0.3 A short circuit current. The built-in buzzer sounds when reading is approximately below 50 mV and audible single tone for normal forward biased diode or semiconductor junction as  $0.3 \text{ V} \leq \text{Reading} \leq 0.8 \text{ V}$ .

## Electrical Specifications

### AC specifications

Function	Range	Resolution	Test current/burden voltage	Accuracy ± (% of reading + counts of least significant digit)		
				40 to 500 Hz	500 Hz to 1 kHz	1 to 2 kHz
AC voltage <sup>1,5</sup> True RMS	1000.0 mV	0.1 mV	-		2% + 5	-
	10.000 V	0.001 V	-	1% + 5		
	100.00 V	0.01 V	-		1% + 5	2% + 5
	1000.0 V	0.1 V	-			-
AC current <sup>2,5</sup> True RMS	1000.0 μA	0.1 μA	< 0.06 V (50 Ω)			
	10000 μA	1 μA	< 0.55 V (50 Ω)	1% + 5		
	100.00 mA	0.01 mA	< 0.18 V (0.5 Ω)		1.5% + 5	-
	440.0 mA <sup>3</sup>	0.1 mA	< 0.8 V (0.5 Ω)			
	10.000 A <sup>4</sup>	0.001 A	< 0.4 V (0.01 Ω)			

1. Input impedance: 10 MΩ (nominal) in parallel with < 100 pF, with overload protection of 1000 V RMS
2. Crest factor ≤ 3. For non-sinusoidal waveforms with crest factor up to 3, add 2% reading + 2% full scale typical.
3. Current can be measured from 50 mA to 440 mA continuously. An additional 0.2% needs to be added to the specified accuracy if the signal measured is in the range of 440 mA to 1100 mA for 30 seconds maximum. After measuring a current of > 440 mA, leave the meter to cool down for twice the measuring time used before application of low current measurement.
4. Current can be measured from 0.5 A up to 10 A continuously with a maximum operating temperature of 50 °C. An additional 0.3% needs to be added to the specified accuracy if the signal measured is in the range of 10 A to 19.999 A for 15 seconds maximum. After measuring a current of >10 A, leave the meter to cool down for 60 seconds before applying a low current measurement.
5. AC voltage and AC current specifications are AC coupled. True RMS measurement is valid from 5 % of range to 100 % of range.

### Temperature specifications

Thermocouple type	Range	Resolution	Accuracy ± (% of reading + offset error)
K (for U1241B and U1242B)	-40 to 1000 °C/-48 to 1832 °F	0.1 °C /0.1 °F	1% + 1 °C/1% + 1.8 °F
J (for U1242B only)	-40 to 1000 °C/-48 to 1832 °F	0.1 °C/0.1 °F	1% + 1 °C/1% + 1.8 °F

### Capacitance specifications

Range	Resolution	Accuracy ± (% of reading + counts of least significant digit)
1000.0 nF	0.1 nF	
10.000 μF	0.001 μF	1.2% + 4
100.00 μF	0.01 μF	
1000.0 μF	0.1 μF	2% + 4
10.000 mF	0.001 mF	

### Harmonic ratio specifications

Range	Frequency	Voltage
0.0% to 99.9%	40 to 500 Hz	100 mVAC to 1000 VAC

## Electrical Specifications

### Switch counter definition

Switch condition <sup>1,2</sup>	Circuit switch	Display <sup>3</sup>	Switch threshold
Low level	Normally close	Lo	< 370 ohms
Intermittent <sup>4</sup>	Close to open	Number of switch count	Low to high transition
High level	Normally open	Hi	> 430 ohms
Intermittent <sup>5</sup>	Open to close	Number of switch count	High to low transition

1. Detects intermittent Opens or Closes lasting for at least 250  $\mu$ sec.
2. Test current of 0.5 mA with maximum open circuit voltage of 2.8 V is used.
3. Maximum count reading: 199.99 M (display "OL" when achieving  $2 \times 10^9$  and thereafter).
4. Count only low to high transition for initial switch condition of Low.
5. Count only high to low transition for initial switch condition of High.

### Frequency specifications

Range	Resolution	Accuracy	Minimum input frequency
100.00 Hz	0.01 Hz	0.03%+3	1 Hz
1000.0 Hz	0.1 Hz		
10.000 kHz	0.001 kHz		
100.00 kHz	0.01 kHz		
1000.0 kHz <sup>1</sup>	0.1 kHz		

1. Effective frequency measurement of up to 200 kHz; refer to frequency sensitivity table below for details.

### Frequency sensitivity during voltage measurement

Input range (Maximum input for specified accuracy = 10 x Range or 1000 V)	Minimum sensitivity (RMS sine wave)	
	20 Hz to 50 kHz	50 to 200 kHz
1000.0 mV	0.3 V	0.6 V
10.000 V	0.5 V	1.8 V
100.00 V	5 V	10 V (< 100 kHz)
1000.0 V	50 V	100 V (< 100 kHz)

### Frequency sensitivity during current measurement

Input range	Minimum sensitivity (RMS sine wave)
	20 Hz to 20 kHz
1000.0 $\mu$ A	100 $\mu$ A
10000 $\mu$ A	500 $\mu$ A
100.00 mA	10 mA
440.00 mA	50 mA
10.000 A	1 A

## Electrical Specifications

### Measuring rate

Function	Times/second
ACV	7
DCV (V or mV)	7
$\Omega$	14
Diode	14
Capacitance	4 (< 100 $\mu$ F)
DCA ( $\mu$ A, mA, A)	7
ACA ( $\mu$ A, mA, A)	7
Temperature	7 (single)
Frequency	1 (> 10 Hz)

## General Specifications

<b>Display</b>	Dual display (secondary display is intended for temperature function display only) consists of 4-digit liquid crystal display (LCD) with maximum reading of 11,000 counts. Automatic polarity indication.
<b>Power consumption</b>	0.22 VA maximum
<b>Battery type and life</b>	Four single standard 1.5 V AAA batteries (Alkaline or Zinc Chloride type); 300 hours typical
<b>Operating environment</b>	Full accuracy at -10 to 55 °C; and to 80% RH for temperatures up to 30 °C, decreasing linearly to 50% RH at 55 °C 0 – 2000 meters per IEC 61010-1 3 <sup>rd</sup> edition CAT III, 1000 V/CAT IV, 600 V IEC 61010-1 3 <sup>rd</sup> edition
<b>Storage compliance</b>	-20 to 70 °C
<b>Safety compliance</b>	IEC 61010-1:2010 / EN 61010-1:2010, IEC 61010-2-033:2012 / EN 61010-2-033:2012 Canada: CAN/CSA-C22.2 No.61010-1-12, CAN/CSA-C22.2 No. 61010-2-033-12 USA: ANSI/UL Std. No. 61010-1 (3rd Edition), ANSI/UL Std. No. 61010-2-033 (1st Edition)
<b>Measurement category</b>	CAT III 1000 V/CAT IV 600 V Overvoltage Protection, Pollution Degree 2
<b>EMC compliance</b>	Commercial limits compliance with EN61326-1 Influence of radiated immunity: In RF electromagnetic fields of 3 V/M  DC voltage measurement typical accuracy: 1000 mV to 1000 V range; $\pm$ 0.2% of range  DC current measurement typical accuracy: 1000 $\mu$ A & 10000 $\mu$ A range; $\pm$ 0.7% of range 100 mA range; $\pm$ 0.22% of range 440 mA range; $\pm$ 0.5% of range 10 A range; $\pm$ 0.11% of range  Note: - If used in close proximity to an RF transmitter or when subjected to continuously present electromagnetic phenomena, some recoverable degradation of performance may occur.
<b>Common Mode Rejection Ratio (CMRR)</b>	> 90 dB at DC, 50/60 Hz $\pm$ 0.1% (1 k $\Omega$ unbalanced)
<b>Normal Mode Rejection Ration (NMRR)</b>	> 60 dB at 50/60 Hz $\pm$ 0.1%
<b>Crest factor</b>	< 3.0
<b>Temperature coefficient</b>	0.1 $\times$ (specified accuracy)/°C (from -10 to 18 °C or 28 to 55 °C)
<b>Shock and vibration</b>	Tested to IEC/EN 60068-2
<b>Dimensions (H x W x D)</b>	193.8 x 92.2 x 58.0 mm
<b>Weight</b>	450 g with batteries 400 g without batteries
<b>Warranty</b>	Three years for main unit Three months for standard shipped accessories

## Ordering Information

### Standard shipped accessories

- Four 1.5 V AAA alkaline batteries
- Certificate of Calibration (CoC)
- Test probe leads (4-mm tips)
- Quick Start Guide
- Free test data (Option UK6)



U1241B



U1242B

### Optional accessories

#### Measuring accessories (non-temperature)

U1161A

Extended test lead kit



Includes two test leads (red and black), two test probes, medium-sized alligator clips and 4-mm banana plugs.

- Test leads: CAT III 1000 V, CAT IV 600 V, 15 A
- Test probes: CAT III 1000 V, CAT IV 600 V, 15 A
- Medium-sized alligator clips: CAT III 1000 V, CAT IV 600 V, 15 A
- 4-mm banana plugs: CAT II 600 V, 10 A

U1162A

Alligator clips



- One pair of insulated alligator clips (red and black). Recommended for use with Keysight standard test leads.
- Rated CAT III 1000 V, CAT IV 600 V, 15 A

U1163A

SMT grabbers



- One pair of SMT grabbers (red and black). Recommended for use with Keysight standard test leads.
- Rated CAT II 300 V, 3 A

U1164A

Fine-tip test probes



- One pair of fine-tip test probes (red and black). Recommended for use with Keysight standard test leads.
- Rated CAT II 300 V, 3 A

U1168A

Standard test lead kit



Includes two test leads (red and black), 19-mm and 4-mm test probes, alligator clips, fine-tip test probes, SMT grabbers and mini grabber (black).

- Test leads: CAT III 1000 V, CAT IV 600 V, 15 A
- Test probes (19-mm tip): CAT II 1000 V, 15 A
- Test probes (4-mm tip): CAT III 1000 V, CAT IV 600 V, 15 A  
**(highly recommended for CAT IV environment)**
- Alligator clips: CAT III 1000 V, CAT IV 600 V, 15 A
- Fine-tip test probes: CAT II 300 V, 3 A
- SMT grabber: CAT II 300 V, 3 A
- Mini grabber: CAT II 300 V, 3 A

U1169A

Test probe leads



Includes two test leads (red and black), and a pair each of 19-mm and 4-mm test probes.

- Test leads: CAT III 1000 V, CAT IV 600 V, 15 A
- Test probes (19-mm tip): CAT II 1000 V, 15 A
- Test probes (4-mm tip): CAT III 1000 V, CAT IV 600 V, 15 A  
**(highly recommended for CAT IV environment)**

U1583B

AC current clamp



- Dual range: 40 A and 400 A
- Rated CAT III 600 V
- BNC-to-banana-plug adapter provided for use with DMMs

## Ordering Information

### Optional accessories

#### Measuring accessories (temperature)

U1180A

Thermocouple adapter+lead kit,  
J and K types



Includes thermocouple adapter, thermocouple bead J-type and thermocouple bead K-type.

- T/C adapter J/K-type
- T/C bead J-type: -20 to 200 °C
- T/C bead K-type: -20 to 200 °C

U1181A

Immersion temperature probe



- Type-K T/C for use in oil and other liquids
- Measurement range: -50 to 700 °C
- Includes adapter U1184A for connection to DMM

U1182A

Industrial surface temperature  
probe



- Type-K T/C for use on still surfaces
- Measurement range: -50 to 400 °C
- Includes adapter U1184A for connection to DMM

U1183A

Air temperature probe



- Type-K T/C for use in air and non-caustic gas
- Measurement range: -50 to 800 °C
- Includes adapter U1184A for connection to DMM

U1184A

Temperature probe adapter



- Mini-connector-to-banana-plug adapter for use with DMM

U1185A

J-type thermocouple and adapter



- T/C adapter J/K-type
- T/C bead J-type: -20 to 200 °C

U1186A

K-type thermocouple and adapter



- T/C adapter J/K-type
- T/C bead J-type: -20 to 200 °C

#### Carrying case

U1172A

Transit case (aluminium-clad)



The robust casing to transport your DMM and accessories

- Aluminum-clad, black panel construction
- Dimension: 18 inches (H) x 13 inches (W) x 6 inches (D)
- Weight: 4 kg

U1174A

Soft carrying case



The convenient way to carry your DMM and essential accessories

- Dimension: 9 inches (H) x 5 inches (W) x 3 inches (D)

#### Hanging kit

U1171A

Magnetic hanging kit



For fastening the DMM to a steel surface so both hands are free

U1179A

IR Connectivity Bracket




Connect with U1177A IR-to-Bluetooth adapter or U1173A IR-USB cable



## Evolving

Our unique combination of hardware, software, support, and people can help you reach your next breakthrough. **We are unlocking the future of technology.**



From Hewlett-Packard to Agilent to Keysight

### myKeysight

#### myKeysight

[www.keysight.com/find/mykeysight](http://www.keysight.com/find/mykeysight)

A personalized view into the information most relevant to you.

### KEYSIGHT SERVICES

Accelerate Technology Adoption.  
Lower costs.

#### Keysight Services

[www.keysight.com/find/service](http://www.keysight.com/find/service)

Our deep offering in design, test, and measurement services deploys an industry-leading array of people, processes, and tools. The result? We help you implement new technologies and engineer improved processes that lower costs.



#### Three-Year Warranty

[www.keysight.com/find/ThreeYearWarranty](http://www.keysight.com/find/ThreeYearWarranty)

Keysight's committed to superior product quality and lower total cost of ownership. Keysight is the only test and measurement company with three-year warranty standard on all instruments, worldwide. And, we provide a one-year warranty on many accessories, calibration devices, systems and custom products.



#### Keysight Assurance Plans

[www.keysight.com/find/AssurancePlans](http://www.keysight.com/find/AssurancePlans)

Up to ten years of protection and no budgetary surprises to ensure your instruments are operating to specification, so you can rely on accurate measurements.

#### Keysight Channel Partners

[www.keysight.com/find/channelpartners](http://www.keysight.com/find/channelpartners)

Get the best of both worlds: Keysight's measurement expertise and product breadth, combined with channel partner convenience.

[www.keysight.com/find/handheldm](http://www.keysight.com/find/handheldm)

For more information on Keysight Technologies' products, applications or services, please contact your local Keysight office. The complete list is available at: [www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)

### Americas

Canada	(877) 894 4414
Brazil	55 11 3351 7010
Mexico	001 800 254 2440
United States	(800) 829 4444

### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 11 2626
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Other AP Countries	(65) 6375 8100

### Europe & Middle East

Austria	0800 001122
Belgium	0800 58580
Finland	0800 523252
France	0805 980333
Germany	0800 6270999
Ireland	1800 832700
Israel	1 809 343051
Italy	800 599100
Luxembourg	+32 800 58580
Netherlands	0800 0233200
Russia	8800 5009286
Spain	800 000154
Sweden	0200 882255
Switzerland	0800 805353
	Opt. 1 (DE)
	Opt. 2 (FR)
	Opt. 3 (IT)
United Kingdom	0800 0260637

For other unlisted countries:  
[www.keysight.com/find/contactus](http://www.keysight.com/find/contactus)  
(BP-10-3-16)



[www.keysight.com/go/quality](http://www.keysight.com/go/quality)

Keysight Technologies, Inc.  
DEKRA Certified ISO 9001:2015  
Quality Management System



Unlocking Measurement Insights

This information is subject to change without notice.  
© Keysight Technologies, 2013 - 2017  
Published in USA, February 21, 2017  
5989-7040EN  
[www.keysight.com](http://www.keysight.com)