

T5 Standard Short

F8W/T5/33-640
0000021

Product features



PRODUCT OVERVIEW

Product name	F8W/T5/33-640
Technology	Fluorescent
Watt (Rated) (W)	7.30
Lamp shape	Tubular shape
Type	T5 Standard Short
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4942351
E-number SE	8356710
E-number Norway	3822411
Luminous flux (lm)	400
Rated lamp efficacy 100h 50Hz at 35°C (lm/W)	55
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	640
CRI (Ra)	64
Colour Variation Initial (SDCM)	SDCM5
Photobiological Risk Group	Not applicable
Wattage (W)	8.00
Product Voltage (V)	56
Dimmable	Yes
Average life (Nominal) (h)	10000
Product EAN number	5410288000213

DATA TABLE

General data

Product name	F8W/T5/33-640
Technology	Fluorescent
Watt (Rated) (W)	7.30

T5 Standard Short

F8W/T5/33-640
0000021

Lamp shape	Tubular shape
Type	T5 Standard Short
Cap/Base	G5
Lamp finish	Frosted/Coated
Fixture rating	Open
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4942351
E-number SE	8356710
E-number Norway	3822411

Optical data

Luminous flux (lm)	400
Luminous flux (Rated) (lm)	400
Rated lamp efficacy 100h 50Hz at 35°C (lm/W)	55
Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	4000
Light colour	Cool White
Colour Code	640
CRI (Ra)	64
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N
Photobiological Risk Group	Not applicable
Rated lumen maint. factor (%) at 2000 h 50Hz	0.88
Rated lumen maint. factor (%) at 4000 h 50Hz	0.82
Rated lumen maint. factor (%) at 6000 h 50Hz	0.78
Rated lumen maint. factor (%) at 8000 h 50Hz	0.75

Electrical data

Wattage (W)	8.00
Watt (Rated) - High frequency (W)	7.1
Current (A)	0.145
Product Voltage (V)	56
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Drive current (mA)	145
Lamp Energy Label (class)	G
kWh per 1000 hours burning time	9

Lifetime data

Average life (Nominal) (h)	10000
Average life (Rated) (h)	10000
Rated survival factor (%) at 2000 h 50Hz	1.00

T5 Standard Short

F8W/T5/33-640
0000021

Rated survival factor (%) at 4000 h 50Hz	0.99
Rated survival factor (%) at 6000 h 50Hz	0.96
Rated survival factor (%) at 8000 h 50Hz	0.83

Physical data

Nominal Product Length (mm)	300.0
Nominal Product Diameter (mm)	16
Max. Length base to base (mm) - A	288.3
Length base to pin Min-Max (mm) - B	293.0-295.4
Max. Lamp Length (mm) - C/L	302.5
Max. Lamp Diameter (mm) - D	17.0
Weight (kg)	0.028


Packaging

Single packaging type	Carton
Product EAN number	5410288000213
Packaging single length / height (cm)	30.6
Packaging single width (cm)	1.9
Packaging single depth (cm)	1.9
DUN14 (inner)	25410288000217
Units per inner package	25
Packaging inner length / height (cm)	32.2
Packaging inner width (cm)	10.0
Packaging inner depth (cm)	10.0
DUN14 (outer)	15410288000210
Units per outer package	500
Packaging outer length / height (cm)	51.2
Packaging outer width (cm)	33.0
Packaging outer depth (cm)	40.8

Safety data


Lamp mercury content (mg)	2.30
Breakage cleaning instructions	Applicable
Recommendation for disposal at end of life	Applicable
Special purpose lamp	No
Suitable for household illumination	Yes

PHOTOMETRY




T5 Standard Short
F8W/T5/33-640
0000021

TECHNICAL DRAWINGS



0000021



8
kWh/1000h




2019/2015

T5 Standard Short
F8W/T5/33-640
0000021



0000021



8
kWh/1000h



2019/2015