

## Knurl cutting tool set A 1

For knurl cutting on lathes and automatic lathes



### Application:

For producing knurl cutting profiles to DIN 82 RAA, RGE 45° and RGE 30° in the steel, stainless steel, non-ferrous metals and cast iron material groups.

### Version:

- set comprising: one each of interchangeable FL/KF head, 1 each of shaft 10x16, 12x16, 16x16, with cemented carbide bushings, setting gauge, instructions for use, cutting data and operating key

### Advantage:

- High flexibility with interchangeable shanks and use as right-hand and left-hand tool on main spindle and counter-spindle
- Clearance-free clamping for high surface quality and service life
- User-friendly setting without disassembly



<b>Art. no.</b>	<b>19100 380</b>
<b>For min. workpiece diameter</b>	3 mm
<b>For max. workpiece diameter</b>	50 mm
<b>Min./max. possible division</b>	0.4-2 mm
<b>Suitable for knurling wheel diameter</b>	14.5 mm
<b>Shaft length</b>	80 mm