

## Table trolley with 3 sheet steel load areas

Welded oil-tight, total carrying capacity 400 kg

**fetra**  
Transportgeräte

### Application:

For the storage and transport of freshly cleaned or oily parts.

### Execution:

- Steel tube and profile steel welded, bolted construction
- Oil-tight trays, edge 40 mm high
- 2 castors and 2 fixed castors, TPE tyres
- Hubs with grooved ball bearings
- Locking device on the castors
- Horizontal sliding handle
- Powder-coated, long-lasting surface protection, impact- and scratch-resistant

### Advantage:

- Avoid the contamination of workstations and floors thanks to oil-tight welded trays



<b>Art. no.</b>	<b>50258 558</b>
<b>Brand</b>	FETRA
<b>Manufacturer Part Number</b>	4832/7016
<b>Design</b>	Welded oil-tight
<b>Material of loading surface</b>	Steel plate
<b>Load-carrying capacity</b>	400 kg
<b>Length</b>	1171 mm
<b>Length x width x height</b>	1171 x 700 x 910 mm
<b>Load-carrying capacity of loading surfaces</b>	200 kg
<b>Number of loading surfaces</b>	3
<b>Loading surface size</b>	1000 x 700 mm
<b>Loading surface length</b>	1000 mm
<b>Loading-surface width</b>	700 mm
<b>Loading-surface height</b>	248 mm, 560 mm, 870 mm
<b>Height</b>	910 mm
<b>Number of fixed rollers</b>	2
<b>Number of steering rollers</b>	2
<b>With wheel lock</b>	Yes
<b>Total stop optional</b>	Yes
<b>Wheel width</b>	40 mm
<b>Wheel diameter</b>	200 mm
<b>Material of wheel</b>	TPE
<b>Colour</b>	Anthracite grey RAL 7016
<b>Surface</b>	Powder-coated
<b>Gross Weight</b>	61.000 kg
<b>Product Group</b>	5AE

### EAN

4017976748320