

SVUC boring bar steel positive, left-hand

For longitudinal and copy turning with VC indexable insert

ATORN[®]

Application

For longitudinal and copy turning with VC indexable insert 35°.

Version

- Precision-made boring bar, **steel**, with internal cooling, type V, attack angle 93°, tip angle 35°, clearance angle 7°

Advantage

- Very narrow geometry optimised for contour-turning work
- Positive body geometry ensures low cutting forces



Art. No.	17849 017
ISO name	A 16 M SVUC R/L 11
Min. bore diameter	21 mm
Shaft diameter	16 mm
Cutting edge height	7.5 mm
Clearance length	16.5 mm
Length	150 mm
Clamping surface height	15 mm
Programming size	11 mm
Suitable for indexable inserts	VC.. 1103..
Tool design	Left

EAN-Code

4050293347401