

Part no. **XNH00-1-S160**
Article no. **183042**

Delivery programme

Basic function			Basic device
Number of poles			1 pole
Mounting type			Busbars of 60 mm
Size			00
Type of connection			Flat connection
Rated operational current	I_e	A	160
Front degree of protection (XNH installed)			IP20 (Operating status) IP2XC (Contact protection) IP10 (Handle cover open)
Rated operational voltage	U_e	V AC	690
Rated operational voltage	U_e	V DC	440
Rated conditional short-circuit current		kA	120 (500 V) 100 (690 V)
Flammability characteristics			Self-extinguishing as per UL 94
Description			Current paths of electrolytic copper, silver-plated Cable connection optionally at the top or bottom

Technical data

Electrical

Standards			IEC/EN 60947-3
Rated operational voltage	U_e	V AC	690
Rated operational voltage	U_e	V DC	440
Rated operational current	I_e	A	160
Rated frequency	f	Hz	40 - 60
Rated insulation voltage	U_i	V AC	800
Total heat dissipation at I_{th} (without fuses)	P_v	W	14
Heat dissipation at 80% (without fuses)	P_v	W	9
Rated impulse withstand voltage	U_{imp}	kV	8
Utilization category AC-23B			
Rated operating voltage	U_e	V AC	400
Rated operating current	I_e	A	160
Utilization category AC22B			
Rated operating voltage	U_e	V AC	500
Rated operating current	I_e	A	160
Utilization category AC-21B			
Rated operating voltage	U_e	V AC	690
Rated operating current	I_e	A	160
Utilization category DC-22B			
Rated operating voltage	U_e	V DC	250
Rated operating current	I_e	A	160
Utilization category DC21B			
Rated operating voltage	U_e	V DC	440
Rated operating current	I_e	A	160
Rated conditional short-circuit current		kA	120 (500 V) 100 (690 V)
Rated short-time withstand current	I_{cw}	kA	7
Max. fuse			
Size according to DIN VDE 0636-2			000 / 00
Max. permitted power loss per fuse link	P_v	W	12

Lifespan, electrical	Operations	300
Mechanical		
Front degree of protection (XNH installed)		IP20 (Operating status) IP2XC (Contact protection) IP10 (Handle cover open)
Ambient temperature	°C	-25 - +55
Rated operating mode		Permanent operation
Activation		Dependent manual activation
Mounting position		Vertical, horizontal
Altitude	m	Max. 2000
Overvoltage category/pollution degree		III/3
RoHS (in accordance with Directive 2002/95/EC of the European Parliament and Council)		Yes
Direction of incoming supply		as required (FLEX System)
Lockable		Yes, optional
Sealable		Yes, Standard
Material characteristics		
Material		Polyamide
Colour		Grey
Flammability characteristics		
Halogen-free		Yes
Voltage test		Yes, sliding inspection windows
Lifespan, mechanical	Operations	1400
Track resistance		CTI 600
Heat deflection temperature	?C	125

Terminal capacity

Flange connection		
Bolt diameter		M8
Cable lug max. width	mm	25
Flat busbar	mm	20 x 10
Box terminal		
Stranded	mm ²	1,5 - 95 Cu
Copper strip	Number of segments x width x thickness	mm 9 x 9 x 0,8
Box terminal		
Stranded	mm ²	1,5 - 50 Cu
Copper band	Number of segments x width x thickness	mm 6 x 9 x 0,8
Clamp-type terminal		
Stranded	mm ²	10 - 70 Cu/Al
Double clamp-type terminal		
Stranded	mm ²	-

Design verification as per IEC/EN 61439


Technical data for design verification			
Rated operational current for specified heat dissipation	I _n	A	160
Heat dissipation per pole, current-dependent	P _{vid}	W	4.7
Equipment heat dissipation, current-dependent	P _{vid}	W	14
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			
10.2.2.1 Verification of thermal stability of enclosures			Meets the product standard's requirements.
10.2.2.2 Verification of resistance of insulating materials to normal heat			Meets the product standard's requirements.
10.2.2.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation		Meets the product standard's requirements.
10.2.5 Lifting		Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 Mechanical impact		Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 Inscriptions		Meets the product standard's requirements.
10.3 Degree of protection of ASSEMBLIES		Does not apply, since the entire switchgear needs to be evaluated.
10.4 Clearances and creepage distances		Is the panel builder's responsibility.
10.5 Protection against electric shock		Does not apply, since the entire switchgear needs to be evaluated.
10.6 Incorporation of switching devices and components		Does not apply, since the entire switchgear needs to be evaluated.
10.7 Internal electrical circuits and connections		Is the panel builder's responsibility.
10.8 Connections for external conductors		Is the panel builder's responsibility.
10.9 Insulation properties		
10.9.2 Power-frequency electric strength		$U_i = 800 \text{ V AC}$
10.9.3 Impulse withstand voltage		Is the panel builder's responsibility.
10.9.4 Testing of enclosures made of insulating material		Is the panel builder's responsibility.
10.10 Temperature rise		The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 Short-circuit rating		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 Electromagnetic compatibility		Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 Mechanical function		The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

Technical data ETIM 6.0

Low-voltage industrial components (EG000017) / Fuse switch disconnecter (EC001040)		
Electric engineering, automation, process control engineering / Low-voltage switch technology / Off-load switch, circuit breaker, control switch / Fuse switch disconnecter (ec ss8.1-27-37-14-01 [AKF058010])		
Version as main switch		Yes
Version as safety switch		Yes
Max. rated operation voltage $U_e \text{ AC}$	V	690
Rated permanent current I_u	A	160
Rated operation power at AC-23, 400 V	kW	64
Conditioned rated short-circuit current I_q	kA	120
Rated short-time withstand current I_{cw}	kA	7
Suitable for fuses		NH00
Number of poles		1
With error protection		No
Type of electrical connection of main circuit		Bolt connection
Suitable for ground mounting		No
Suitable for front mounting 4-hole		Yes
Suitable for busbar mounting		Yes
Type of control element		Cover grip
Position control element		Front side
Motor drive optional		No
Motor drive integrated		No
Version as emergency stop installation		No
Degree of protection (IP), front side		IP2X

Dimensions



Additional product information (links)

IL0131118ZU Fuse switch-disconnector XNH

IL0131118ZU Fuse switch-disconnector XNH ftp://ftp.moeller.net/DOCUMENTATION/AWA_INSTRUCTIONS/IL0131118ZU2015_11.pdf