

MIRO 6.2 24VDC-1U OUTPUT RELAY


IN: 24 VDC - OUT: 250 VAC/DC / 6 A

1 NO/NC contact
24 V DC
Spring clamp terminals




When the max. switching voltage/current is exceeded the gold plating is destroyed. The relay will then take on the properties of an output type.

[Link to Product](#)

Illustration



stay connected



Product may differ from Image

Approvals



Utilization category

AC-12	6 A (24/110/230 V AC)
AC-15	3 A (24/110/230 V AC)

The information in this brochure has been compiled with the utmost care. Liability for the correctness completeness and topicality of the information is restricted to gross negligence. Version: 05/15

DC-13 1 A (24 V DC); 0.2 A (110 V DC); 0.1 A (230 V DC)

Input

Connection voltage - current 24 V DC (19.2...30 V DC) - 14 mA

LED display LED (green)

General data

Mech./ elect. life 20.000.000 switching cycles/load dependent

Test isolation voltage 4 kV; safe separation (EN 60947-1)

Mounting method DIN-rail mountable (EN 60715)

Temperature range -20...+55 °C

Dimensions H x W x D 90x6.2x65 mm

Output

Switching voltage max. 250 V AC/DC

Switching current per output max. 6 A

Min. load current 100 mA (12 V DC)

Power rating (voltage dependent) max. 1500 VA/120 W

Switching frequency max. 10 Hz

Energize/release/contact bounce time 10/15/1.5 ms

Contact material Ag Sn O₂**Commercial data**

country of origin CZ

customs tariff number 85364900

minimum order quantity 1