


KAGER – Thermax® Precision Temperature Indicators

KAGER – Thermax Precision Temperature Indicators are simple, cost-effective temperature monitoring program based on proprietary colour change technologies.

Irreversible temperature indicators provide a permanent record that an item has reached or exceeded its rated temperature. They can be used in applications where specific temperature bands are required.



Features

- Clear colour change shows maximum temperature experienced
- Permanent record of highest temperature
- Immediate response to temperature
- Cost effective temperature monitoring solution
- Oil, water, and steam resistant

Benefits

- Easy to read – Distinct colour change when temperature been exceeded (Clear to BLACK)
- Distinct separation of temperature ranges for improved readability
- Easy to use – Product arrives ready to use. No pre-activation required.
- Precise temperature bands for improved measurement accuracy

KAGER – Thermax® Precision Temperature Indicators

Key Specifications:	
Temperature Range:	+25 to +300° C
Accuracy:	+ 25 to +100° C: +/- 1,0° C +104 to +150° C: +/- 1,5° C +154 to +200° C: +/- 3,0° C +204 to +300° C: +/- 4,0° C
Size:	22 x 55 mm vertical
Visual Indication:	Colour change clear to black
Mounting:	Self Adhesive
Storage Requirements:	Store in a cool dry space, below lowest temperature level

Application Examples:


Proof of Drying, Curing & Bonding –
confirmation that appropriate temperatures
have been reached



Preventative Maintenance – monitoring of
machine components



Warranty Claims – indication of equipment
overheating



Process Validation – verification that in-
process temperatures have been achieved

