

GN 817.1 | Indexing plungers with flange

Zinc alloy and stainless steel



- 1
- 2
- 3
- 4
- 5
- 6
- 7
- 8
- 9
- 10
- 11
- 12
- 13
- 14
- 15
- 16
- 17
- 18

BASE FLANGE

Die-cast zinc alloy, black epoxy resin coating, matte finish.

PLUNGER

Nickel-plated AISI 303 stainless steel.

SPRING

AISI 301 stainless steel.

KNOB

High-resilience polyamide based (PA) technopolymer, black colour, matte finish.

STANDARD EXECUTIONS

- **GN 817.1-B**: without rest position.
- **GN 817.1-C**: with rest position.

FEATURES AND APPLICATIONS

GN 817.1-C indexing plungers are used for applications requiring the plunger locked in the retracted position. By retracting and turning the knob by 90°, the plunger remains retracted.


SPECIAL EXECUTIONS ON REQUEST

Indexing plungers with red clamping knob (GN 817.1-RT).



GN 817.1-B

GN 817.1-C



Code	Description	d1										Spring preload [N]	Spring max load [N]	⚖️
		Plunger -0.02 -0.04 Hole +0.10 +0.03	d2	d3	d4	b	k	l1	l2	l3	l4			
GN.34641	GN 817.1-6-6-B	6	23	4.3	34	13	22	6	48	22	6	6.5	19	38
GN.34642	GN 817.1-6-6-C	6	23	4.3	34	13	22	6	48	22	6	6.5	19	40
GN.34643	GN 817.1-6-9-B	6	23	4.3	34	13	22	9	48	22	6	6	25	38
GN.34644	GN 817.1-6-9-C	6	23	4.3	34	13	22	9	48	22	6	6	25	41
GN.34647	GN 817.1-8-8-B	8	28	5.3	38	16	26	8	58	26	8	8.5	26	69
GN.34648	GN 817.1-8-8-C	8	28	5.3	38	16	26	8	58	26	8	8.5	26	73
GN.34645	GN 817.1-8-12-B	8	28	5.3	38	16	26	12	58	26	8	8.5	28	68
GN.34646	GN 817.1-8-12-C	8	28	5.3	38	16	26	12	58	26	8	8.5	28	70
GN.34649	GN 817.1-10-12-B	10	28	5.3	38	16	26	12	58	26	8	9.5	38	70
GN.34650	GN 817.1-10-12-C	10	28	5.3	38	16	26	12	58	26	8	9.5	38	75