

SCSC clamping holder, positive, right

For longitudinal turning with CC indexable insert

ATORN[®]

Application


For longitudinal turning with CC indexable insert, 80°

Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



Art. no.	17830 833
ISO name	SCSC R/L 1010 E06
Shaft height	10 mm
Shank width	10 mm
Length	70 mm
Length of head	12 mm
Programming size	12 mm
Suitable for indexable inserts	CC.. 0602..
Tool design	Left

EAN-Code

4050293562811