

### Product type designation



### CP 5613 A3

COMMUNICATION PROCESSOR CP 5613 A3, PCI-CARD (32BIT; 3.3/5V; 33/66MHZ); WITH ONE INTERFACE FOR CONNECT. TO PROFIBUS; INCL. CONFIGURATION TOOL AND DP-BASE SOFTWARE: DP-RAM INTERFACE FOR DP-MASTER; INCL. PG- AND FDL-PROTOCOL; SINGLE LICENSE FOR 1 INSTALLAT. RUNTIME SOFTWARE, CLASS A; SW + ELECTR. MANUALS ON DVD 2-LANGUAGES (G,E); SUPPORT FOR OPERATING SYSTEM SEE SIMATIC NET SOFTWARE V12

### Transmission rate

#### Transfer rate

- |   |                          |
|---|--------------------------|
| <ul style="list-style-type: none"> <li>at the 1st interface / acc. to PROFIBUS</li> </ul> | 9.6 kbit/s ... 12 Mbit/s |
|---|--------------------------|

### Interfaces

#### Number of electrical connections

- |   |   |
|---|---|
| <ul style="list-style-type: none"> <li>at the 1st interface / acc. to PROFIBUS</li> </ul> | 1 |
|---|---|

#### Type of electrical connection

- |   |                             |
|---|-----------------------------|
| <ul style="list-style-type: none"> <li>at the 1st interface / acc. to PROFIBUS</li> </ul> | 9-pin Sub-D socket (RS 485) |
|---|-----------------------------|

### Supply voltage, current consumption, power loss

#### Type of voltage / of the supply voltage

DC
----

#### Supply voltage

- |  |       |
|--|-------|
| <ul style="list-style-type: none"> <li>1 / from backplane bus</li> </ul> | 3.3 V |
| <ul style="list-style-type: none"> <li>2 / from backplane bus</li> </ul> | 12 V  |

#### Relative symmetrical tolerance / for DC

- |  |     |
|--|-----|
| <ul style="list-style-type: none"> <li>at 3.3 V</li> </ul> | 9 % |
| <ul style="list-style-type: none"> <li>at 12 V</li> </ul>  | 8 % |

#### Consumed current

- |   |        |
|---|--------|
| <ul style="list-style-type: none"> <li>1 / from backplane bus / for DC / maximum</li> </ul> | 0.15 A |
| <ul style="list-style-type: none"> <li>2 / from backplane bus / for DC / maximum</li> </ul> | 0.25 A |

#### Active power loss

3.5 W
-------

### Permitted ambient conditions

#### Ambient temperature

- |  |             |
|--|-------------|
| <ul style="list-style-type: none"> <li>during operation</li> </ul> | 5 ... 55 °C |
|--|-------------|

<ul style="list-style-type: none"> <li>during storage</li> </ul>	-20 ... +60 °C
<ul style="list-style-type: none"> <li>during transport</li> </ul>	-20 ... +60 °C
Relative humidity / at 25 °C / without condensation / during operation / maximum	85 %
Protection class IP	IP00

### Design, dimensions and weight

Module format	PCI
Width	18 mm
Height	107 mm
Depth	125 mm
Net weight	0.098 kg
Number of plug-in cards of same design / plug-in / per PC station	4
Number of units / Note	-

### Performance data

#### Performance data / open communication

Software / for open communication / by means of SEND/RECEIVE / required	FDL driver included in scope of delivery of the CP
Number of possible connections / for open communication / by means of SEND/RECEIVE / maximum	80

#### Performance data / PROFIBUS DP

Software / for DP master function / required	No
Service / as DP master	
<ul style="list-style-type: none"> <li>DPV0</li> </ul>	Yes
<ul style="list-style-type: none"> <li>DPV1</li> </ul>	Yes
<ul style="list-style-type: none"> <li>DPV2</li> </ul>	Yes
Number of DP slaves / on DP master / usable	124
Amount of data	
<ul style="list-style-type: none"> <li>of the address area of the inputs / as DP master / total</li> </ul>	30256 byte
<ul style="list-style-type: none"> <li>of the address area of the outputs / as DP master / total</li> </ul>	30256 byte
<ul style="list-style-type: none"> <li>of the address area of the inputs / per DP slave</li> </ul>	244 byte
<ul style="list-style-type: none"> <li>of the address area of the outputs / per DP slave</li> </ul>	244 byte
<ul style="list-style-type: none"> <li>of the address area of the diagnostic data / per DP slave</li> </ul>	244 byte
Software / for DP slave function / required	No
Service / as DP slave	
<ul style="list-style-type: none"> <li>DPV0</li> </ul>	Yes
<ul style="list-style-type: none"> <li>DPV1</li> </ul>	Yes

Amount of data	
<ul style="list-style-type: none"> <li>• of the address area of the inputs / as DP slave / total</li> </ul>	244 byte
<ul style="list-style-type: none"> <li>• of the address area of the outputs / as DP slave / total</li> </ul>	244 byte

### Performance data / S7 communication

Software / for S7 communication / required	Yes, HARDNET-PB S7 (S7-5613)
Number of possible connections / for S7/PG communication / maximum	50

### Performance data / multi-protocol mode

Number of active connections / with multi-protocol mode	50
Number of configurable connections / per PC station	207

### Product functions / management, configuration

Configuration software / required	Included in scope of supply
-----------------------------------	-----------------------------

### Product functions / Diagnosis

Product function	
<ul style="list-style-type: none"> <li>• Port diagnostics</li> </ul>	Yes

### Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> <li>• for EMC</li> </ul>	89/336/EEC
<ul style="list-style-type: none"> <li>• for safety / from CSA and UL</li> </ul>	CAN/CSA C22.2 & UL 60950-1, UL 1950
<ul style="list-style-type: none"> <li>• for emitted interference</li> </ul>	EN 61000-6-3
<ul style="list-style-type: none"> <li>• for interference immunity</li> </ul>	EN 61000-6-2
Certificate of suitability	
<ul style="list-style-type: none"> <li>• CE marking</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• C-Tick</li> </ul>	Yes

### Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> <li>• to website: Selector SIMATIC NET SELECTION TOOL</li> </ul>	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a>
<ul style="list-style-type: none"> <li>• to website: Industrial communication</li> </ul>	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
<ul style="list-style-type: none"> <li>• to website: Industry Mall</li> </ul>	<a href="http://www.siemens.com/industrial-controls/mall">http://www.siemens.com/industrial-controls/mall</a>
<ul style="list-style-type: none"> <li>• to website: Information and Download Center</li> </ul>	<a href="http://www.siemens.com/automation/net/catalog">http://www.siemens.com/automation/net/catalog</a>
<ul style="list-style-type: none"> <li>• to website: Image database</li> </ul>	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
<ul style="list-style-type: none"> <li>• to website: CAx Download Manager</li> </ul>	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
<ul style="list-style-type: none"> <li>• to website: Industry Online Support</li> </ul>	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>

### Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

**last modified:**

09.03.2015