

## Blind rivet nut box

GBM 10 model



### Version:

- Set with manual blind rivet nut tool GBM 10
- With M4, M5 and M6 threaded mandrel and nosepiece
- Various blind rivet nut sizes from M4-M6, aluminium
- For riveting material thicknesses from 0.25-3 mm

### Advantage:

- Simple to adjust the stroke using the knurled nut with stroke scale for secure and complete placement of the blind rivet nut
- Rapid replacement of threaded mandrels without the need for tools

### Delivery:

With 3 nosepieces, in sheet steel case



<b>Art. no.</b>	<b>53195 350</b>
<b>Model</b>	GBM 10
<b>Length</b>	260 mm
<b>Suitable for max. rivet diameter (rivet material: aluminium)</b>	6 mm
<b>Suitable for max. rivet diameter (rivet material: stainless steel)</b>	6 mm

### EAN-Code

4007081530019