



Manufacturers Part Number	Cross Sectional Area	Length	Hole Sizes	Stamped Number	Nominal Braid Width
TBL-1.1-100-M4	1.1mm ²	100	M4	2.5-4	2mm
TBL-2.5-100-M4	2.5mm ²	100	M4	4-4	6mm
TBL-2.5-150-M4	2.5mm ²	150	M4	4-4	6mm
TBL-4.3-100-M4	4.3mm ²	100	M4	6-4	9mm
TBL-4.3-150-M4	4.3mm ²	150	M4	6-4	9mm
TBL-6.0-150-M4	6mm ²	150	M4	10-4	10mm
TBL-6.0-200-M4	6mm ²	200	M4	10-4	10mm
TBL-6.0-150-M5	6mm ²	150	M5	10-5	10mm
TBL-6.0-200-M5	6mm ²	200	M5	10-5	10mm
TBL-10-150-M6	10mm ²	150	M6	16-6	13mm
TBL-10-200-M6	10mm ²	200	M6	16-6	13mm
TBL-10-200-M8	10mm ²	200	M8	16-8	13mm
TBL-16-200-M6	16mm ²	200	M6	25-6	20mm
TBL-16-200-M8	16mm ²	200	M8	25-8	20mm
TBL-16-250-M8	16mm ²	250	M8	25-8	20mm
TBL-16-500-M8	16mm ²	500	M8	25-8	20mm
TBL-25-200-M8	25mm ²	200	M8	35-8	25mm
TBL-25-300-M8	25mm ²	300	M8	35-8	25mm
TBL-25-500-M8	25mm ²	500	M8	35-8	25mm
TBL-35-200-M8	35mm ²	200	M8	50-8	28mm
TBL-35-300-M8	35mm ²	300	M8	50-8	28mm
TBL-35-500-M8	35mm ²	500	M8	50-8	28mm

Please be aware that the dimensions and details mentioned within this data sheet are nominal and should be used as a guide only

Whilst every effort has been made to ensure that the information contained in this publication is correct. IS-Cabletec and its agents will not accept any liability or responsibility for any costs or damages whatsoever arising directly or indirectly from the use or misuse of the products or information contained in this publication. Users must independently ascertain the suitability of the product to meet their requirements. IS-Cabletec reserve the right to change the product specification without notice. IS-Cabletec's obligations are limited to those indicated in our standard terms and conditions of sale, available on our website