



Miniature circuit breaker 230 V 6kA, 1+N-pole C, 16A Version Italy

Model	
product brand name	SETRON
product designation	Miniature circuit breaker
design of the product	5SL miniature circuit breakers
General technical data	
number of poles	2
number of poles / note	1P+N
tripping characteristic class	C
mechanical service life (switching cycles) / typical	10 000
overvoltage category	III
degree of pollution	2
Voltage	
insulation voltage	
• with single-phase operation / at AC / rated value	250 V
Supply voltage	
type of voltage	AC
operational current / at AC / rated value	16 A
supply voltage / at AC / rated value	230 V
operating voltage	
• at DC / rated value / maximum	72 V
supply voltage frequency	
• rated value	50 Hz
Protection class	
protection class IP	IP20, with connected conductors
Switching capacity	
switching capacity current	
• acc. to EN 60898 / rated value	6 kA
• acc. to IEC 60947-2 / rated value	6 kA
energy limitation class	3
Dissipation	
power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.5 W
suitability for operation	Residential buildings/infrastructure
Product details	
product function / neutral conductor switching	Yes
product feature / touch protection	Yes
product feature	

• halogen-free	Yes
• sealable	Yes
• silicon-free	Yes
product extension / installable / supplementary devices	Yes

Connections

connectable conductor cross-section / solid	
• minimum	0.75 mm ²
• maximum	25 mm ²
connectable conductor cross-section / stranded	
• minimum	0.75 mm ²
• maximum	25 mm ²
connectable conductor cross-section / finely stranded / with core end processing	
• minimum	0.75 mm ²
• maximum	25 mm ²
tightening torque / with screw-type terminals	
• minimum	2.5 N·m
• maximum	3 N·m

Mechanical Design

height	90 mm
width	36 mm
depth	76 mm
installation depth	70 mm
number of modular width units	2
mounting position	any
net weight	295 g

Environmental conditions

influence of the surrounding temperature	Periodically +55°C, max. 95% humidity
ambient temperature	
• minimum	-25 °C
• maximum	45 °C
ambient temperature / during storage	
• minimum	-40 °C
• maximum	75 °C

Certificates

reference code	
• acc. to DIN EN 61346-2	F
• acc. to IEC 81346-2	F

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mfb=5SL6516-7BB>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SL6516-7BB>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5SL6516-7BB

Tender specifications

<http://www.siemens.com/specifications>

